



AOC G3 25G3ZM/BK computer monitor 62.2 cm (24.5") 1920 x 1080 pixels Full HD Black, Red

Brand : AOC

Product family: G3

Product code: 25G3ZM/BK

Product name : 25G3ZM/BK

Screen size (inch) 24.5, Panel resolution 1920x1080, Refresh rate 240 Hz, Response time MPRT 0.5 ms, Panel type VA, HDMI HDMI 2.0 x 2, Display Port DisplayPort 1.2 x 1, Sync technology (VRR) Adaptive Sync



AOC G3 25G3ZM/BK computer monitor 62.2 cm (24.5") 1920 x 1080 pixels Full HD Black, Red:

24.5" FHD VA display with Adaptive Sync, low input lag and 1 ms GTG

The AOC 25G3ZM/BK meets the needs of both eSports, competitive gamers, and casual gamers as well. It offers a responsive 24.5" VA panel with FHD resolution, ShadowControl and super contrast ratio of 3000:1. Be the fastest in action with 240Hz refresh rate, Adaptive Sync, 1ms GTG and low input lag. AOC G3 25G3ZM/BK. Display diagonal: 62.2 cm (24.5"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Response time: 1 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. VESA mounting, Height adjustment. Product colour: Black, Red



Display		Ergonomics	
Display diagonal *	62.2 cm (24.5")	Cable lock slot *	✓
Display resolution *	1920 x 1080 pixels	Cable lock slot type	Kensington
HD type *	Full HD	Height adjustment *	✓
Native aspect ratio *	16:9	Adjustable height (max)	13 cm
Panel type *	VA	Pivot	✓
LED backlight	✓	Swivelling	✓
Backlight type	W-LED	Swivel angle range	-30 - 30°
Touchscreen *	✗	Tilt adjustment	✓
Display brightness (typical)	300 cd/m²	Tilt angle range	-5 - 23°
Response time *	1 ms	On Screen Display (OSD)	✓
Response time measurement type	GTG (Gray to Gray)	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Croatian, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Ukrainian
Response time (MPRT)	0.5 ms		
Anti-glare screen	✓		
Screen shape *	Flat		
Contrast ratio (typical) *	3000:1		
Contrast ratio (dynamic)	80000000:1	Power	
Maximum refresh rate *	240 Hz	Energy efficiency class (SDR) *	E
Viewing angle, horizontal	178°	Energy consumption (SDR) per 1000 hours *	18 kWh
Viewing angle, vertical	178°	Power consumption (typical) *	25 W
Display number of colours *	16.7 million colours	Power consumption (standby) *	0.3 W
Pixel density	90 ppi	Power consumption (off)	0.3 W
Display diagonal (metric)	62.23 cm	Power supply type	Internal
Colour gamut standard	DCI-P3	Energy efficiency scale	A to G
Colour gamut	92%	Weight & dimensions	
sRGB coverage (typical)	100%	Width (with stand)	557.3 mm
DCI-P3 coverage	92%	Depth (with stand)	258.8 mm
Performance		Height (with stand)	503 mm
NVIDIA G-SYNC *	✗		

Performance		Weight & dimensions	
AMD FreeSync *	✓	Weight (with stand)	4.24 kg
AMD FreeSync type	FreeSync Premium	Width (without stand)	557.3 mm
AMD FreeSync refresh rate range	48 - 240 Hz	Depth (without stand)	48 mm
Flicker-free technology	✓	Height (without stand)	328.9 mm
Low Blue Light technology	✓	Packaging data	
Game mode	✓	Package width	620 mm
Multimedia		Package depth	160 mm
Built-in speaker(s) *	✗	Package height	541 mm
Built-in microphone	✗	Package weight	6.34 kg
Design		Packaging content	
Market positioning *	Gaming	Cables included	AC, HDMI, DisplayPort
Product colour *	Black, Red	DisplayPort cable length	1.8 m
Front bezel colour	Black/Red	HDMI cable length	1.8 m
Detachable stand	✓	Sustainability	
Ports & interfaces		Doesn't contain	Mercury, PVC/BFR
HDMI *	✓	Other features	
HDMI ports quantity	2	Brand specific technologies	Crosshair
HDMI version	2.0	Low input lag	✓
DisplayPorts quantity	1	FPS counter	✓
DisplayPort version	1.2	Dial point	✓
Headphone out *	✓	Shadow control	✓
Headphone connectivity	3.5 mm	Motion blur reduction	✓
Ergonomics		Exterior finish type	Matt
VESA mounting *	✓	Bezel thickness type	Frameless
Panel mounting interface	100 x 100 mm	Warranty period	3 year(s)
		Compliance certificates	CE
		Certification	WEEE,REACH compliant,RoHs compliant,CB,TUV-Bauart-Mark,ISO 9241-307,EAC,FCC,Microsoft WHQL



4038986140911

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.