

ASUS ProArt PA32UCX-PK computer monitor 81.3 cm (32") 3840 x 2160 pixels 4K Ultra HD LED Black

Brand : ASUS

Product family: ProArt

Product code: 90LM03HC-B01370

Product name : PA32UCX-PK

32", 16:9, IPS, 3840x2160, 600 cd/m², 5ms, 2 x Thunderbolt™ 3 USB-C™, 3 x HDMI, DisplayPort, 9.7 kg
ASUS ProArt PA32UCX-PK. Display diagonal: 81.3 cm (32"), Display resolution: 3840 x 2160 pixels, HD type: 4K Ultra HD, Display technology: LED, Display surface: Matt, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	81.3 cm (32")	DisplayPorts quantity	1
Display resolution *	3840 x 2160 pixels	DisplayPort version	1.2
HD type *	4K Ultra HD	Thunderbolt 3 ports quantity	2
Native aspect ratio *	16:9	Headphone out *	✓
Display technology *	LED	Headphone outputs	1
Panel type *	IPS	Headphone connectivity	3.5 mm
Touchscreen *	✗	HDCP	✓
Display brightness (typical)	600 cd/m²	Ergonomics	
Response time *	5 ms	VESA mounting *	✓
Display surface	Matt	Panel mounting interface	100 x 100 mm
Screen shape *	Flat	Cable lock slot *	✓
Supported graphics resolutions	3840 x 2160	Cable lock slot type	Kensington
Aspect ratio	16:9	Height adjustment *	✓
Contrast ratio (typical) *	1000:1	Adjustable height (max)	13 cm
Contrast ratio (dynamic)	1000000:1	Pivot	✓
Dynamic contrast ratio marketing name	SmartContrast	Pivot angle	-90 - 90°
Maximum refresh rate *	142 Hz	Swivelling	✓
Viewing angle, horizontal	178°	Swivel angle range	-60 - 60°
Viewing angle, vertical	178°	Tilt adjustment	✓
Display number of colours *	1.073 billion colours	Tilt angle range	-5 - 23°
Pixel pitch	0.1845 x 0.1845 mm	Picture-in-Picture	✓
Viewable size, horizontal	70.8 cm	Power	
Viewable size, vertical	39.9 cm	Energy efficiency class (SDR) *	G
Digital horizontal frequency	109 - 142 kHz	Energy efficiency class (HDR) *	G
Digital vertical frequency	29 - 65 Hz	Energy consumption (SDR) per 1000 hours *	80 kWh
High Dynamic Range (HDR) supported	✓	Energy consumption (HDR) per 1000 hours *	97 kWh
High Dynamic Range (HDR) technology	High Dynamic Range (HDR) 1000	Power consumption (standby) *	0.5 W
Colour gamut standard	sRGB	Power consumption (off)	0.3 W
sRGB coverage (typical)	100%	AC input voltage	100 - 240 V
Adobe RGB coverage	99.5%		

Performance		Power	
Flicker-free technology	✓	AC input frequency	50 - 60 Hz
Low Blue Light technology	✓	Energy efficiency scale	A to G
Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	727 mm
RMS rated power	3 W	Depth (with stand)	240 mm
Built-in speaker(s) *	✓	Height (with stand)	600 mm
Built-in camera *	✗	Weight (with stand)	14.6 kg
Design		Width (without stand)	727 mm
Market positioning *	Graphics design	Depth (without stand)	93 mm
Product colour *	Black	Height (without stand)	426 mm
Feet colour	Black	Weight (without stand)	9.7 kg
Ports & interfaces		Packaging data	
Built-in USB hub *	✓	Package width	913 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package depth	525 mm
USB upstream port type	USB Type-C	Package height	381 mm
Number of upstream ports	1	Package weight	19.8 kg
USB Type-A downstream ports quantity	3	Packaging content	
USB Type-C downstream ports quantity	1	Stand included	✓
DVI port	✗	Cables included	AC
HDMI *	✓	Other features	
HDMI ports quantity	3	Certification	BSMI, CB, CCC, CEL level 0, CU, ErP, FCC, ISO-9241-307, J-MOSS, KCC, Mac CompliantPSE, UkrSEPRO, UL/cUL, VCCI, WEEE, WHQL (Windows 10, Windows 8.1, Windows 7), MEPS, RCM, TUV Flicker-free , KC , eStandby, TUV Low Blue Light, ICES-3, PC recycle, VESA DisplayHDR 1000
HDMI version	2.0b		
		Logistics data	
		Harmonized System (HS) code	85285210



4718017693585



4718017693561



4718017749381

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.