

NETGEAR GSM4248PX-100EUS network switch Managed L2/L3/L4 Gigabit Ethernet (10/100/1000) Power over Ethernet (PoE) Black

Brand : NETGEAR

Product code: GSM4248PX-100EUS

Product name : GSM4248PX-100EUS

- Dedicated AV web-based GUI
 - Clean integration in AV racks
 - Standard or recessed mounting with all ports in the back, or all ports in the front
- 10/100/1000BASE-T, RJ-45, PoE+, 960W, 240Gbps, RS-232, SFP+
NETGEAR GSM4248PX-100EUS. Switch type: Managed, Switch layer: L2/L3/L4. Basic switching RJ-45 Ethernet ports type: Gigabit Ethernet (10/100/1000), Basic switching RJ-45 Ethernet ports quantity: 48. Switching capacity: 240 Gbit/s. Power over Ethernet (PoE). Rack mounting

Management features		Design	
Switch type *	Managed	Product colour	Black
Switch layer	L2/L3/L4	Power	
Quality of Service (QoS) support	✓	Power supply included *	✓
Web-based management	✓	Power over Ethernet (PoE)	
Ports & interfaces		Power over Ethernet (PoE) *	✓
Basic switching RJ-45 Ethernet ports quantity *	48	Power over Ethernet plus (PoE+) ports quantity	40
Basic switching RJ-45 Ethernet ports type *	Gigabit Ethernet (10/100/1000)	Total Power over Ethernet (PoE) budget	960 W
SFP+ module slots quantity	8	Weight & dimensions	
Data transmission		Width	440 mm
Switching capacity *	240 Gbit/s	Depth	43.2 mm
Design		Height	400 mm
Rack mounting *	✓	Weight	6.31 kg
Stackable *	✓	Logistics data	
		Harmonized System (HS) code	85176990



0606449151732



606449151732

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.