

Targus AWU314BGLZ mobile device dock station Tablet Black

Brand : Targus

Product code: AWU314BGLZ

Product name : AWU314BGLZ

- Modular base supports a range of docking or hub add-ons (sold separately)
 - Allows tablet to rotate 350-degrees and tilt 90-degrees
 - Includes 5.9 ft USB-C cable to connect to monitor
 - Integrated standard base lock slot and tablet lock safeguards equipment
 - Secure hinge prevents cradle removal
 - Requires Targus Tablet Case for Samsung Galaxy Tab Active Pro (THD501GLZ, sold separately)
 - Works with Targus Locking Plate (BPLATE1, sold separately) to securely attach to a desk
 - Works with most smart Type-C monitors to transform your tablet into a desktop experience through the Samsung DeX software
- Tablet Cradle Workstation for Samsung Galaxy Tab Active Pro
Targus AWU314BGLZ. Basic device type: Tablet, Brand compatibility: Samsung, Compatibility: Galaxy Tab Active Pro. Docking connector type: USB Type-C. Width: 230 mm, Depth: 245 mm, Height: 295 mm, Weight: 2.3 kg. Product colour: Black



Performance		Ports & interfaces	
Basic device type *	Tablet	Audio output *	✗
Brand compatibility *	Samsung	HDMI *	✗
Compatibility	Galaxy Tab Active Pro	Power	
Product colour	Black	Power source type	USB
Card reader integrated	✗	Weight & dimensions	
Number of displays supported	1	Width	230 mm
Windows operating systems supported	✓	Depth	245 mm
Mac operating systems supported	✓	Height	295 mm
Network		Weight	2.3 kg
Bluetooth *	✗	Packaging data	
Ethernet LAN	✗	Quantity	1
Ports & interfaces		Packaging content	
Docking connector type *	USB Type-C	Cables included	USB Type-C
USB Type-C ports quantity	1	Logistics data	
		Country of origin	Taiwan
		Harmonized System (HS) code	84719000



5051794035339



0092636353278



092636353278

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.