



Canon PIXMA GM4050 Inkjet A4 600 x 1200 DPI Wi-Fi

Brand : Canon

Product family: PIXMA

Product code: 3111C008

Product name : GM4050

- High-yield refillable ink tank, 18000 pages (3 black ink bottles)
- Auto 2-sided printing
- 35-sheet ADF, 350-sheet plain paper capacity via a 2-way feed
- Ethernet and Wi-Fi connectivity
- Sharp black text

- 2-line mono LCD and remote management tools

4 functions (print, copy, scan, ADF), 350-sheet capacity, Refillable ink tanks, Mobile Printing, Cloud Link, Wi-Fi, Ethernet, LCD display

Canon PIXMA GM4050. Print technology: Inkjet, Printing: Mono printing, Maximum resolution: 600 x 1200 DPI. Copying: Mono copying. Scanning: Colour scanning, Optical scanning resolution: 1200 x 2400 DPI.

Maximum ISO A-series paper size: A4. Wi-Fi. Product colour: Black



Printing		Ports & interfaces	
Duplex printing mode	Auto	USB port	✓
Print technology *	Inkjet	USB connector	USB Type-B
Printing *	Mono printing	USB 2.0 ports quantity	1
Duplex printing *	✓	Network	
Maximum resolution *	600 x 1200 DPI	Wi-Fi *	✓
Print speed (ISO/IEC 24734) mono	13 ipm	Ethernet LAN *	✓
Print speed (ISO/IEC 24734) colour	6.8 ipm	Cabling technology	10/100Base-T(X)
Copying		Ethernet LAN data rates	100 Mbit/s
Duplex copying *	✗	Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
Copying *	Mono copying	Security algorithms	WEP, WPA-PSK, WPA2-PSK
Maximum number of copies	99 copies	Mobile printing technologies	PIXMA Cloud Link
Copier resize	25 - 400%	Design	
N-in-1 copy function	✓	Product colour *	Black
N-in-1 copy function (N=)	2, 4	Market positioning *	Home & office
ID-card copy function	✓	Built-in display *	✓
Scanning		Display	LCD
Scanning *	Colour scanning	Control type	Buttons
Optical scanning resolution *	1200 x 2400 DPI	Colour display	✗
Maximum scan area	216 x 297 mm	Power	
Scanner type *	Flatbed & ADF scanner	Power consumption (printing)	10 W
Scan technology	CIS	Power consumption (standby)	0.8 W
Scan to	Image	Power consumption (off)	0.3 W
Input colour depth	16 bit	Energy Star Typical Electricity Consumption (TEC)	0.14 kWh/week
Output colour depth	8 bit	AC input voltage	100 - 240 V
Input greyscale depth	16 bit	AC input frequency	50 - 60 Hz
Output greyscale depth	8 bit		

Fax		System requirements	
Faxing *	✗	Windows operating systems supported	Windows 10, Windows 7, Windows 8.1
Features		Server operating systems supported	Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016
Ink tank system	✓	Mobile operating systems supported	Android, iOS
Number of print cartridges *	1	Operational conditions	
Printing colours *	Black	Operating relative humidity (H-H)	10 - 90%
Replacement cartridges	GI-50, CL-541, CL-541XL	Operating temperature (T-T)	5 - 35 °C
Input & output capacity		Sustainability	
Total number of input trays *	1	Sustainability certificates	ENERGY STAR
Total input capacity *	100 sheets	Weight & dimensions	
Auto document feeder (ADF)	✓	Width	403 mm
Auto document feeder (ADF) input capacity	35 sheets	Depth	369 mm
Maximum input capacity	250 sheets	Height	234 mm
Paper handling		Weight	9.2 kg
Maximum ISO A-series paper size *	A4	Packaging content	
Paper tray media types *	Envelopes, High resolution paper, Plain paper	Cartridge(s) included	✓
ISO A-series sizes (A0...A9) *	A4, A5	Included cartridge capacity (black)	600 pages
ISO B-series sizes (B0...B9)	B5	Included cartridge capacity (CMY)	400 pages
Envelopes sizes	Com-10, DL	Cables included	AC
Borderless printing media sizes	A4, A5, B5, Letter	Bundled software	MP Driver, IJ Printer Assistant Tool
Custom media width	55 - 215.9 mm	Logistics data	
Custom media length	89 - 676 mm	Harmonized System (HS) code	84433100
Paper tray media weight	64 - 105 g/m²		



4549292152562

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.