Epson UltraChrome Pro 12 ink cartridge 1 pc(s) Original Yellow



Brand : Epson

Product code: C13T44Q440

Product name : UltraChrome Pro 12

UltraChrome Ink – 350ml Y Ink Cartridge (P7560/P9560)

Epson UltraChrome Pro 12 ink cartridge 1 pc(s) Original Yellow:

UltraChrome Pro12 ink is based on Epson's famous K3 and HDR ink. It has an aqueous (water based) all-pigment construction that has been designed for professional and commercial print production. The formulation provides an extended gamut with superior colour accuracy and archival level image stability.

Ink dries quickly to produce prints that are water and scratch resistant. The ink set includes Vivid Magenta for brighter blues and pinks as well as Light and Dark Grey for improved balance with neutral greys, reduced bronzing and minimal colourcasts/colour twist.

The Pro formulation features improved Matte and Photo Black inks that provide an enhanced Dmax for brighter prints with an enhanced tonal range in both B/W and colour. It also features a new Yellow ink that provides further durability enhancement with increased UV light resistance. With the addition of the Violet ink cartridge this ink set can offer 99% Pantone coverage.

Features	
Compatibility *	SureColor P7560/P9560
Quantity per pack *	1 pc(s)
Colour ink volume	350 ml
Type *	Original
Printing colours *	Yellow
Brand compatibility *	Epson
Country of origin	Indonesia
Packaging data	
Package width	450 mm
Package depth	245 mm

Packaging data	
Package height	115 mm
Package weight	0.57 g
Logistics data	
Master (outer) case width	490 mm
Master (outer) case length	350 mm
Master (outer) case height	190 mm
Products per master (outer) case	24 pc(s)
Master (outer) case gross weight	9.5 g
Harmonized System (HS) code	84439990

8715946668772

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date