

Epson EB-L260F Standard throw projector 4600 ANSI lumens 3LCD 1080p (1920x1080) White

Brand : Epson

Product code: V11HA69080

Product name : EB-L260F

- 4,600 lumens brightness display Full HD crisp images and bright colours, even in well-lit rooms
 - A scalable display Flexible scalable display from 31 inches up to 310 inches
 - Stream content easily Wireless, MTR auto power-on by HDMI and easy smart stick connection
 - Fit and forget reliability Easy installation with multi-projection and signage function
 - The complete solution With an incredible contrast ratio of 2,500,000:1, the EB-L260F delivers vivid, lifelike content and defined shadow detail with deeper blacks
- 4600 - 3200 Lumen, 1080p, 16:9, 2500000:1, 10 Bits, 192 Hz - 240 Hz, 260W, AC 220-240 V, 50-60 Hz



Projector		Network	
Screen size compatibility *	787.4 - 7874 mm (31 - 310")	Wi-Fi *	✓
Projection distance (wide)	0.9 - 9.1 m	Wi-Fi standards	Wi-Fi 5 (802.11ac)
Projector brightness *	4600 ANSI lumens	Miracast	✓
Projection technology *	3LCD	Features	
Projector native resolution *	1080p (1920x1080)	Noise level (economic mode)	27 dB
Contrast ratio (typical) *	2500000:1	HDCP	✓
Native aspect ratio *	16:9	Projection modes	Ceiling, Front
Number of colours	1.07 billion colours	On Screen Display (OSD)	✓
Projector brightness (economic mode)	3200 ANSI lumens	Screen mirroring	✓
Vertical scan range	192 - 240 Hz	Noise level *	37 dB
Keystone correction, horizontal	30°	Air filter	✓
Keystone correction, vertical	30°	Password protection	✓
Heat dissipation	884 BTU/h	Multimedia	
Light source		Built-in speaker(s) *	✓
Light source type *	Laser	RMS rated power	16 W
Service life of light source *	20000 h	Design	
Service life of light source (economic mode)	30000 h	Product type *	Standard throw projector
Lens system		Product colour *	White
Focus *	Manual	Placement	Ceiling, Desktop, Floor, Wall
Focal length range	18.2 - 29.1 mm	Cable lock slot	✓
Aperture range (F-F)	1.51 - 1.77	Cable lock slot type	Kensington
Zoom capability	✓	Power	
Zoom type	Manual	Power source *	AC
Zoom ratio	1:1.62	Power consumption (typical) *	199 W
Throw ratio	1.32 - 2.12:1	Power consumption (standby) *	0.5 W
Offset	1000%	Power consumption (max)	260 W
Video		Power consumption (economy mode)	144 W
Full HD *	✓	AC input voltage	220 - 240 V
Video colour modes	Blackboard, DICOM simulation mode, Dynamic, Multi-projection, Presentation, sRGB	AC input frequency	50 - 60 Hz
Ports & interfaces		Operational conditions	
USB 2.0 ports quantity	2	Storage temperature (T-T)	-10 - 60 °C
USB 2.0 Type-A ports quantity	1	Operating relative humidity (H-H)	20 - 80%
Audio (L/R) in *	2	Storage relative humidity (H-H)	10 - 90%

Ports & interfaces		Weight & dimensions	
Audio (L/R) out	1	Width	325 mm
Microphone in	✓	Depth	299 mm
Serial interface type *	RS-232C	Height	90 mm
VGA (D-Sub) ports quantity *	3	Weight *	4.2 kg
HDMI ports quantity *	2	Packaging content	
Composite video in *	1	Remote control included *	✓
AC (power) in	✓	Batteries included	✓
Audio Return Channel (ARC)	✓	Cables included	HDMI, Power
Network		Epson Creative Projection, EasyMP Multi PC Projection, Epson Projector Content Manager, Epson Projector Management	
Ethernet LAN *	✓	Bundled software	
Ethernet LAN (RJ-45) ports	1	Logistics data	
		Quantity per pack	1 pc(s)



8715946715452

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.