



LG 40WP95CP-W computer monitor 100.8 cm (39.7") 5120 x 2160 pixels 5K Ultra HD LED Yellow

Brand : LG

Product code: 40WP95CP-W.AEK

Product name : 40WP95CP-W

- 39.7-inch 5K2K (5120x2160) UltraWide™
- Nano IPS Display with DCI-P3 98% (Typ.), HDR10
- Thunderbolt™ 4, USB 3.0
- 5K Daisy Chain
- Auto Brightness (Ambient light sensor)
- HW Calibration

39.7" 5K UHD 5120x2160, IPS, 300 cd/m², 26W, HDMI, DisplayPort, USB, 12.3kg

LG 40WP95CP-W. Display diagonal: 100.8 cm (39.7"), Display resolution: 5120 x 2160 pixels, HD type: 5K Ultra HD, Display technology: LED, Response time: 5 ms, Native aspect ratio: 21:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub. VESA mounting, Height adjustment. Product colour: Yellow



Display		Ports & interfaces	
Display diagonal *	100.8 cm (39.7")	DisplayPorts quantity	1
Display resolution *	5120 x 2160 pixels	DisplayPort version	1.4
HD type *	5K Ultra HD	Thunderbolt 4 ports quantity	1
Native aspect ratio *	21:9	Headphone out *	✓
Display technology *	LED	HDCP	✓
Panel type *	IPS	HDCP version	2.2
Backlight type	Edge LED	Ergonomics	
Touchscreen *	✗	VESA mounting *	✓
Display brightness (typical)	300 cd/m²	Panel mounting interface	100 x 100 mm
Response time *	5 ms	Height adjustment *	✓
Anti-glare screen	✓	Adjustable height (max)	11 cm
Screen shape *	Curved	Swivel angle range	-15 - 15°
Contrast ratio (typical) *	1000:1	Tilt adjustment	✓
Maximum refresh rate *	60 Hz	Tilt angle range	-5 - 20°
Viewing angle, horizontal	178°	On Screen Display (OSD)	✓
Viewing angle, vertical	178°	Power	
Display number of colours *	1.07 billion colours	Energy efficiency class (SDR) *	F
Pixel pitch	0.1815 x 0.1815 mm	Energy efficiency class (HDR) *	G
Display diagonal (metric)	101 cm	Energy consumption (SDR) per 1000 hours *	40 kWh
High Dynamic Range (HDR) supported	✓	Energy consumption (HDR) per 1000 hours *	72 kWh
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)	Power consumption (typical) *	80 W
Surface hardness	3H	Power consumption (standby) *	1.2 W
Colour depth	10 bit	Power consumption (max)	88 W
Colour gamut standard	DCI-P3	Power consumption (off)	0.3 W
Colour gamut	98%	Power consumption (PowerSave)	57 W
Performance		Power supply type	Internal
AMD FreeSync *	✓	Energy efficiency scale	A to G
AMD FreeSync type	FreeSync	Weight & dimensions	
Flicker-free technology	✓	Width (with stand)	947.2 mm
Smart modes	Energy saving	Depth (with stand)	283 mm
Multimedia		Height (with stand)	614.7 mm
Number of speakers	2	Weight (with stand)	12.3 kg
RMS rated power	10 W		

Multimedia		Weight & dimensions	
Built-in speaker(s) *	✓	Width (without stand)	947.2 mm
Design		Depth (without stand)	114.8 mm
Product colour *	Yellow	Height (without stand)	419.2 mm
Front bezel colour	White	Weight (without stand)	10.2 kg
Detachable stand	✓	Packaging data	
Feet colour	Silver	Package width	1050 mm
Ports & interfaces		Package depth	250 mm
Built-in USB hub *	✓	Package height	510 mm
Number of upstream ports	1	Package weight	16.6 kg
USB Type-A downstream ports quantity	2	Package type	Box
USB Power Delivery (USB PD)	✓	Packaging content	
USB Power Delivery up to	96 W	Stand included	✓
HDMI *	✓	Cables included	AC, DisplayPort, HDMI, Thunderbolt, USB Type-C
HDMI ports quantity	2	Other features	
HDMI version	2.2	Country of origin	South Korea



8806084017956

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.