

ASUS BE24ECSNK computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD Black

Brand : ASUS

Product code: 90LM05M1-B0A370

Product name : BE24ECSNK

- Best for video conferencing and online learning with integrated Full HD webcam, mic array and stereo speakers
 - 23.8-inch Full HD(1920x1080) frameless IPS panel with wide viewing angles
 - ASUS AI Noise-Canceling Microphone offers crystal-clear voice communication
 - Face Auto Exposure technology helps users' face to stand out from the background and keep the image crisp
 - Extensive connectivity with HDMI, USB-C, DisplayPort, DisplayPort out for daisy-chain, earphone jack, USB hub and RJ45 LAN port for the most flexibility
 - USB-C port allows simple laptop docking for data transmission and video signal to the display, as well as charging the laptop via just one cable
 - Zoom Certified monitor has undergone comprehensive testing and review processes to ensure seamless communication
- 23.8" Full HD 1920 x 1080 IPS, 16.7M, 5ms, 60Hz, USB-C, HDMI, VESA



Display		Ports & interfaces	
Display diagonal *	60.5 cm (23.8")	HDMI ports quantity	1
Display resolution *	1920 x 1080 pixels	HDMI version	1.4
HD type *	Full HD	Headphone out *	✓
Native aspect ratio *	16:9	Headphone outputs	1
Panel type *	IPS	HDCP	✓
Backlight type	LED	HDCP version	1.4
Touchscreen *	✗	Charging port type	USB Type-C
Display brightness (typical)	300 cd/m²	Ergonomics	
Response time *	5 ms	VESA mounting *	✓
Display surface	Matt	Panel mounting interface	100 x 100 mm
Screen shape *	Flat	Cable lock slot *	✓
Contrast ratio (typical) *	1000:1	Cable lock slot type	Kensington
Contrast ratio (dynamic)	100000000:1	Height adjustment *	✓
Dynamic contrast ratio marketing name	ASUS Smart Contrast Ratio (ASCR)	Adjustable height (max)	15 cm
Maximum refresh rate *	60 Hz	Pivot	✓
Viewing angle, horizontal	178°	Pivot angle	90 - -90°
Viewing angle, vertical	178°	Swivelling	✓
Display number of colours *	16.7 million colours	Swivel angle range	180 - -180°
Pixel pitch	0.2745 x 0.2745 mm	Tilt adjustment	✓
Viewable size, horizontal	52.7 cm	Tilt angle range	35 - -5°
Viewable size, vertical	29.6 cm	Power	
Performance		Energy efficiency class (SDR) *	E
NVIDIA G-SYNC *	✗	Energy consumption (SDR) per 1000 hours *	18 kWh
AMD FreeSync *	✗	Power consumption (typical) *	17.7 W
Flicker-free technology	✓	Power consumption (off)	0.5 W
Low Blue Light technology	✓	Power consumption (PowerSave)	0.5 W

Multimedia		Power	
Number of speakers	2	Energy efficiency scale	A to G
RMS rated power	2 W	Weight & dimensions	
Built-in speaker(s) *	✓	Width (with stand)	539.7 mm
Megapixel (approx.)	2 MP	Depth (with stand)	211.4 mm
Built-in camera *	✓	Height (with stand)	538.9 mm
Design		Weight (with stand)	6.5 kg
Market positioning *	Business	Width (without stand)	539.7 mm
Product colour *	Black	Depth (without stand)	61 mm
Ports & interfaces		Height (without stand)	389.9 mm
Built-in USB hub *	✓	Weight (without stand)	4.3 kg
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Packaging data	
USB upstream port type	USB Type-C	Package width	722 mm
Number of upstream ports	1	Package depth	481 mm
Number of USB Type-C upstream ports quantity	1	Package height	182 mm
USB Type-A downstream ports quantity	4	Package weight	8.9 kg
USB Type-C DisplayPort Alternate Mode	✓	Package type	Box
USB Power Delivery (USB PD)	✓	Packaging content	
USB Power Delivery up to	80 W	Stand included	✓
HDMI *	✓	Sustainability	
		Sustainability certificates	TCO
		Other features	
		RJ-45 ports quantity	1



4711081650669



0195553564137



195553564137

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.