

TP-Link AXE5400 Wi-Fi 6E Bluetooth 5.3 PCIe Adapter

Brand : TP-Link

Product code: ARCHER TXE72E

Product name : AXE5400 Wi-Fi 6E Bluetooth 5.3 PCIe Adapter

IEEE 802.11a/b/g/n/ac/ax, 2.4/5/6 GHz, 55 x 36 x 11.5 mm

TP-Link AXE5400 Wi-Fi 6E Bluetooth 5.3 PCIe Adapter. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: WLAN / Bluetooth. Maximum data transfer rate: 2402 Mbit/s, Top Wi-Fi standard: Wi-Fi 6E (802.11ax), Wi-Fi band: Tri-band (2.4 GHz / 5 GHz / 6 GHz). Antenna type: 2x2, Product colour: Black



Ports & interfaces		System requirements	
Connectivity technology *	Wired	Windows operating systems supported	Windows 10 Education x64, Windows 10 Enterprise x64, Windows 10 Home x64, Windows 10 x64, Windows 11, Windows 11 Enterprise x64, Windows 11 x64
Host interface *	PCI Express		
Interface *	WLAN / Bluetooth		
Network		Operational conditions	
Maximum data transfer rate *	2402 Mbit/s	Operating temperature (T-T)	0 - 40 °C
Networking standards *	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11ax, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n	Operating relative humidity (H-H)	10 - 90%
Wi-Fi	✓	Storage relative humidity (H-H)	5 - 95%
Wi-Fi band	Tri-band (2.4 GHz / 5 GHz / 6 GHz)	Sustainability	
Top Wi-Fi standard	Wi-Fi 6E (802.11ax)	Sustainability compliance	✓
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6E (802.11ax)	Weight & dimensions	
WLAN data transfer rates supported	54,300,1732,2402 Mbit/s	Width	78.5 mm
Security algorithms	WEP, WPA, WPA-PSK, WPA2, WPA2-PSK, WPA3	Depth	21 mm
Bluetooth	✓	Height	120 mm
Bluetooth version	5.3	Packaging data	
Design		Package width	201.5 mm
Component for *	PC	Package depth	152.5 mm
Product colour	Black	Package height	41.5 mm
Internal *	✓	Package weight	240 g
Antenna	✓	Packaging content	
Antenna design	External	Mounting brackets included	✓
Antenna type	2x2	Resource CD	✓
Transmitting power (CE)	5 GHz: 15, 2.4 GHz: 16	Bluetooth header cable	✓
Transmitting power (FCC)	5 GHz: 20, 2.4 GHz: 20, 6 GHz: 12	Quick installation guide	✓
Operating modes	Infrastructure mode		

Technical details

Compliance certificates

CE, Federal Communications
Commission (FCC), RoHS



4897098688380



0840030708381



840030708381



4897098688397

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.