



AOC E2 U34E2M/BK computer monitor 86.4 cm (34") 3440 x 1440 pixels UltraWide Quad HD LED Black

Brand : AOC

Product family: E2

Product code: U34E2M/BK

Product name : U34E2M/BK



Screen size (inch) 34, Panel resolution 3440x1440, Refresh rate 100 Hz, Panel type VA, HDMI HDMI 2.0 x 2, Display Port DisplayPort 1.2 x 1, D-SUB (VGA) 0x, DVI 0x, Sync technology (VRR) Adaptive Sync

AOC E2 U34E2M/BK computer monitor 86.4 cm (34") 3440 x 1440 pixels UltraWide Quad HD LED Black:

34" VA monitor with WQHD and slim 3 side frameless design for a comfortable and neat look

The AOC U34E2M is equipped with a 34" VA panel with Ultrawide QHD 21:9 resolution for an incredible viewing experience and more screen estate to boost your productivity and multitasking. Multiple inputs supported thanks to HDMI and DP ports.

AOC E2 U34E2M/BK. Display diagonal: 86.4 cm (34"), Display resolution: 3440 x 1440 pixels, HD type: UltraWide Quad HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 21:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. VESA mounting. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	86.4 cm (34")	Headphone outputs	1
Display resolution *	3440 x 1440 pixels	Headphone connectivity	3.5 mm
HD type *	UltraWide Quad HD	Built-in KVM switch	✗
Native aspect ratio *	21:9	AC (power) in	✓
Display technology *	LED	Mobile High-Definition Link (MHL)	✗
Panel type *	VA	Network	
LED backlight	✓	Ethernet LAN	✗
Backlight type	W-LED	Ergonomics	
Touchscreen *	✗	VESA mounting *	✓
Display brightness (typical)	300 cd/m²	Panel mounting interface	100 x 100 mm
Response time *	4 ms	Cable lock slot *	✓
Response time measurement type	GTG (Gray to Gray)	Cable lock slot type	Kensington
Anti-glare screen	✓	Pivot	✗
Screen shape *	Flat	Tilt adjustment	✓
Contrast ratio (typical) *	4000:1	Tilt angle range	3.5 - 21.5°
Contrast ratio (dynamic)	20000000:1	LED indicators	✓
Maximum refresh rate *	100 Hz	Power	
Viewing angle, horizontal	178°	Energy efficiency class (SDR) *	F
Viewing angle, vertical	178°	Power consumption (typical) *	35 W
Display number of colours *	16.7 million colours	Power consumption (standby) *	0.5 W
Pixel pitch	0.23175 x 0.23175 mm	Power consumption (off)	0.3 W
Pixel density	109.7 ppi	Power supply type	Internal
Display diagonal (metric)	86.4 cm	Weight & dimensions	
Surface hardness	3H	Width (with stand)	817.5 mm
sRGB coverage (typical)	115%	Depth (with stand)	253.8 mm
NTSC coverage (typical)	100%	Height (with stand)	475 mm
Adobe RGB coverage	98%		
DCI-P3 coverage	91%		

Performance		Weight & dimensions	
NVIDIA G-SYNC *	✗	Weight (with stand)	7.67 kg
Fast charging	✗	Width (without stand)	817.5 mm
VESA Adaptive Sync support	✓	Depth (without stand)	55.3 mm
Flicker-free technology	✓	Height (without stand)	370.7 mm
Low Blue Light technology	✓	Packaging data	
Multimedia		Package width	940 mm
Built-in speaker(s) *	✗	Package depth	174 mm
Built-in microphone	✗	Package height	506 mm
Built-in camera *	✗	Package weight	10.7 kg
Design		Package type	Box
Market positioning *	Office	Packaging content	
Product colour *	Black	Stand included	✓
Front bezel colour	Black	Cables included	AC, HDMI
Detachable stand	✓	HDMI cable length	1.8 m
Ports & interfaces		Other features	
Built-in USB hub *	✗	Low input lag	✗
DVI port	✗	FPS counter	✗
HDMI *	✓	Dial point	✗
HDMI ports quantity	2	Shadow control	✗
HDMI version	2.0	Motion blur reduction	✗
DisplayPorts quantity	1	Picture-by-Picture (PbP)	✓
DisplayPort version	1.2	Exterior finish type	Matt
Headphone out *	✓	Bezel thickness type	Frameless
		Warranty period	3 year(s)
		Light effects	✗
		Supplied AC adapter type	False



4038986110723

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.