



AOC E3 Q27E3UAM computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD Black

Brand : AOC

Product family: E3

Product code: Q27E3UAM

Product name : Q27E3UAM

- 4 ms response time GtG
- VA
- 24"
- FHD (1920x1080 px)
- Low blue light
- Flicker-Free

Screen size (inch) 27, Panel resolution 2560x1440, Refresh rate 75 Hz, Panel type VA, HDMI HDMI 1.4 x 1, Display Port DisplayPort 1.2 x 1, D-SUB (VGA) 0x, DVI 0x, Sync technology (VRR) Adaptive Sync

AOC E3 Q27E3UAM computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD Black:

27" QHD VA display with essential features for long hours of productivity

The AOC Q27E3UAM offers a great 27" VA panel with wide viewing angle, detailed and crystal-clear QHD resolution and 300 nits brightness. It also offers all essentials for working or studying, supporting long hours with features for eye care such as Low Blue Mode and Flicker Free. For a neatwork station, it also offers cable management for its complete connectivity.



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	Headphone out *	✓
Display resolution *	2560 x 1440 pixels	Headphone connectivity	3.5 mm
HD type *	Quad HD	Built-in KVM switch	✗
Native aspect ratio *	16:9	HDCP	✓
Panel type *	VA	HDCP version	1.4
LED backlight	✓	Network	
Backlight type	W-LED	Ethernet LAN	✗
Touchscreen *	✗	Ergonomics	
Response time *	4 ms	VESA mounting *	✓
Response time measurement type	GTG (Gray to Gray)	Panel mounting interface	100 x 100 mm
Anti-glare screen	✓	Cable lock slot *	✓
Screen shape *	Flat	Cable lock slot type	Kensington
Contrast ratio (typical) *	4000:1	Height adjustment *	✗
Contrast ratio (dynamic)	20000000:1	Pivot	✗
Maximum refresh rate *	75 Hz	Tilt adjustment	✓
Viewing angle, horizontal	178°	Tilt angle range	5 - 23°
Viewing angle, vertical	178°	On Screen Display (OSD)	✓
Display number of colours *	16.7 million colours	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish
Pixel pitch	0.2331 x 0.2331 mm		
Pixel density	109 ppi	Power	
Display diagonal (metric)	68.6 cm	Energy efficiency class (SDR) *	F
Surface hardness	3H	Power consumption (typical) *	16.92 W
sRGB coverage (typical)	112%	Power consumption (standby) *	0.5 W
NTSC coverage (typical)	97%		
Adobe RGB coverage	96%		
Performance			
NVIDIA G-SYNC *	✗		
AMD FreeSync *	✗		

Performance		Power	
Fast charging	✓	Power consumption (off)	0.3 W
Flicker-free technology	✓	AC input voltage	100 - 240 V
Low Blue Light technology	✓	AC input frequency	50/60 Hz
		Power supply type	Internal
Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	614.7 mm
RMS rated power	4 W	Depth (with stand)	201.3 mm
Built-in speaker(s) *	✓	Height (with stand)	449.1 mm
Built-in microphone	✗	Weight (with stand)	4.43 kg
Built-in camera *	✗	Width (without stand)	614.7 mm
		Depth (without stand)	52.8 mm
		Height (without stand)	369.6 mm
Design		Packaging data	
Market positioning *	Home	Package width	452 mm
Product colour *	Black	Package depth	142 mm
Frameless design	✓	Package height	691 mm
Front bezel colour	Black	Package weight	7.65 kg
Detachable stand	✓		
Ports & interfaces		Packaging content	
Built-in USB hub *	✓	Stand included	✓
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Cables included	AC, HDMI
USB Type-A downstream ports quantity	2	HDMI cable length	1.8 m
DVI port	✗	Power cable length	1.8 m
HDMI *	✓		
HDMI ports quantity	1	Other features	
HDMI version	1.4	Low input lag	✗
DisplayPorts quantity	1	FPS counter	✗
DisplayPort version	1.2	Dial point	✗
Audio input	✓	Shadow control	✗
		Motion blur reduction	✗
		Exterior finish type	Textured
		Bezel thickness type	Frameless
		Warranty period	3 year(s)
		Light effects	✗
		Supplied AC adapter type	False



4038986180689

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.