



QNAP Card QM2 interface cards/adapter Internal PCIe, RJ-45

Brand : QNAP
Product code: QM2-2P410G2T
Product name : Card QM2

- M.2 SSDs* can be installed (no tools required) to form caching pools or an auto-tiering volume
 - Enables SSD caching to boost performance and optimizes storage efficiency with Qtier Technology**
 - Provides 10GBASE-T connectivity and backwards compatibility with 5GbE/2.5GbE/1GbE/100MbE
 - M.2 SSD thermal sensors allow real-time M.2 SSD temperature monitoring
 - A quiet cooling module (heatsink and smart fan) minimizes overheating risks and sustains constant high performance
 - LED indicators for monitoring M.2 SSD status
- 2 x M.2 PCIe Gen4 NVMe SSD & 2 x 10GbE ports expansion cards

QNAP Card QM2 interface cards/adapter Internal PCIe, RJ-45:

Future-proof 10GbE network environments
The QM2-2P410G1T features a 10GBASE-T Multi-Gigabit (10G/5G/2.5G/1G/100M) network port to empower your QNAP NAS with 10GbE high-speed connectivity for bandwidth-demanding tasks. With QNAP's various 10GbE switches, you can easily upgrade to a high-speed network environment.

Ports & interfaces		Design	
Host interface *	M.2	Purpose	NAS / Storage server
Output interface *	PCIe, RJ-45	Number of expansion slots	2
Expansion card form factor	Low-profile	LED indicators	SSD, Status
Expansion card standard	PCIe 4.0	Weight & dimensions	
NVMe	✓	Width	187 mm
Serial interface type	RJ-45	Depth	68.9 mm
Design		Height	19.4 mm
Internal *	✓	Logistics data	
		Harmonized System (HS) code	84733020



0885022022410



885022022410



4711103080061

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.