

ASUS BE24ECSBT computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Touchscreen Black

Brand : ASUS

Product code: 90LM05M1-B0B370

Product name : BE24ECSBT

- 23.8-inch Full HD(1920x1080) frameless IPS panel with wide viewing angles
- 10-point multi-touch capacity delivers smooth and intuitive touch experience
- Extensive connectivity with USB-C with power delivery, HDMI, DisplayPort in and out for daisy-chain, Earphone jack and USB hub for the most flexibility
- Ergonomic design with +35° ~ -5° tilt, ±180° swivel, ±90° pivot and 130mm height adjustments for a comfortable viewing experience
- USB-C port allows simple laptop docking for data transmission and video signal to the display, as well as up to 80W power delivery to the laptop via just one cable

ASUS BE24ECSBT Multi-touch Monitor - 24 inch (23.8 inch viewable), FHD (1920x1080), 10-point Touch, IPS, USB-C with Power Delivery, HDMI, DisplayPort Daisy Chain, Height Adjustable, Ergonomic Stand, Eye Care, Low Blue Light, Flicker Free, Wall Mountable, Auto Brightness Adjustment



Display		Ports & interfaces	
Display diagonal *	60.5 cm (23.8")	USB Power Delivery up to	80 W
Display resolution *	1920 x 1080 pixels	HDMI *	✓
HD type *	Full HD	HDMI ports quantity	1
Native aspect ratio *	16:9	HDMI version	1.4
Display technology *	LED	DisplayPorts quantity	2
Panel type *	IPS	DisplayPort version	1.4
Backlight type	LED	Headphone out *	✓
Touchscreen *	✓	HDCP	✓
Display brightness (typical)	300 cd/m²	HDCP version	1.4
Response time *	5 ms	Charging port type	USB Type-C
Anti-glare screen	✓	Ergonomics	
Screen shape *	Flat	VESA mounting *	✓
Contrast ratio (typical) *	1000:1	Panel mounting interface	100 x 100 mm
Maximum refresh rate *	75 Hz	Cable lock slot *	✓
Viewing angle, horizontal	178°	Cable lock slot type	Kensington
Viewing angle, vertical	178°	Height adjustment *	✓
Display number of colours *	16.7 million colours	Adjustable height (max)	13 cm
Pixel pitch	0.2745 x 0.2745 mm	Pivot	✓
Viewable size, horizontal	52.7 cm	Pivot angle	-90 - 90°
Viewable size, vertical	29.6 cm	Swivelling	✓
Colour gamut standard	sRGB	Swivel angle range	-180 - 180°
Colour gamut	100%	Tilt angle range	-5 - 35°
Performance		Power	
NVIDIA G-SYNC *	✗	Power consumption (typical) *	17.7 W
AMD FreeSync *	✗	Power consumption (off)	0 W
Flicker-free technology	✓	Power consumption (PowerSave)	0.5 W
Low Blue Light technology	✓	AC input voltage	100 - 240 V

Multimedia		Power	
Number of speakers	2	AC input frequency	50 - 60 Hz
RMS rated power	4 W	Weight & dimensions	
Built-in speaker(s) *	✓	Width (with stand)	539.7 mm
Built-in camera *	✗	Depth (with stand)	211.4 mm
Design		Height (with stand)	459.4 mm
Market positioning *	Business	Weight (with stand)	6.1 kg
Product colour *	Black	Width (without stand)	539.7 mm
Feet colour	Black	Depth (without stand)	52.8 mm
Ports & interfaces		Height (without stand)	329.9 mm
Built-in USB hub *	✓	Weight (without stand)	4.1 kg
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Packaging data	
USB upstream port type	USB Type-C	Package width	746 mm
USB Type-A downstream ports quantity	3	Package depth	170 mm
USB Type-C DisplayPort Alternate Mode	✓	Package height	440 mm
USB Power Delivery (USB PD)	✓	Package weight	8.3 kg
		Package type	Box
		Packaging content	
		Stand included	✓



4711081905448



0195553905459



195553905459

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.