

Epson 107 Original

Brand : Epson

Product code: C13T09B440

Product name : 107

- High quality prints
- Ultra-low-cost
- 107 EcoTank Yellow ink bottle

Epson 107 Original:

High-quality photo printing

This six-colour, dye-based ink set delivers smooth tonal gradations and deeper, more natural blacks, detailed high-contrast images and natural skin tones. The 70ml ink bottles provide an abundant supply of ink so you can print lots of professional-looking, glossy photos at your convenience without worrying about costs or running out of ink.

Unleash your creativity

Feel free to print your photos without worrying about the cost with this ink series. From the first set of inks included with your EcoTank printer, you'll have enough ink to print up to 2,100 (10x15cm) photos ^[1].

The genuine article

Enjoy hassle-free and reliable printing with Epson's genuine inks. We invest in extensive research, high-tech manufacturing facilities and put our products through rigorous tests, to deliver the best quality product for you.



Features		Technical details	
Type *	Original	Pallet net length	120 cm
Printing colours *	Yellow	Pallet net width	80 cm
Colour ink volume	70 ml	Master (outer) cases per pallet layer (EU)	5 pc(s)
Brand compatibility *	Epson	Products per pallet (EU)	45 pc(s)
Compatibility *	EcoTank ET-18100	Layers per pallet	9 pc(s)
Packaging data		Master (outer) cases per pallet layer	7 pc(s)
Quantity per pack *	1 pc(s)	Logistics data	
Package width	57 mm	Products per pallet	1890 pc(s)
Package depth	57 mm	Pallet gross length	120 cm
Package height	177 mm	Pallet gross width	100 cm
Package weight	130 g	Pallet gross height	15 cm
Package type	Box	Products per pallet layer	63 pc(s)
Technical details		Products per pallet (UK)	1350 pc(s)
Master (outer) case GTIN (EAN/UPC)	8715946712161	Harmonized System (HS) code	32159000900
Pallet net height	15 cm		



8715946712369



8715946712420

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.