



DELL Smart-UPS SRT 3000VA RM uninterruptible power supply (UPS) Double-conversion (Online) 3 kVA 2700 W 10 AC outlet(s)

Brand : DELL

Product code: A9088192



Product name : Smart-UPS SRT 3000VA RM


- Avoids costly power problems
 - Low operating and maintenance costs
 - Reliability and intelligent battery management
- Smart-UPS SRT 3000VA RM - UPS - 2700-watt - 3000 VA - Lead Acid

DELL Smart-UPS SRT 3000VA RM uninterruptible power supply (UPS) Double-conversion (Online) 3 kVA 2700 W 10 AC outlet(s):

Network-grade power conditioning protects from damaging surges and disruptive noise. The double conversion architecture provides tight voltage regulation, frequency regulation, and zero transfer time to battery during power events.

DELL Smart-UPS SRT 3000VA RM. UPS topology: Double-conversion (Online), Output power capacity: 3 kVA, Output power: 2700 W. AC outlet types: C13 coupler, C19 coupler, Power plug: C20 coupler, AC outlets quantity: 10 AC outlet(s). Battery technology: Sealed Lead Acid (VRLA). Form factor: Rackmount, Product colour: Black, Rack capacity: 2U. Width: 432 mm, Depth: 635 mm, Height: 85 mm


Features		Ports & interfaces	
UPS topology *	Double-conversion (Online)	USB port	✓
Output power capacity *	3 kVA	USB port type	USB Type-B
Output power *	2700 W	Serial interface	✓
Waveform *	Sine	Serial interface type	RS-232
Input operation voltage (min) *	100 V	Ethernet LAN (RJ-45) ports	2
Input operation voltage (max) *	275 V	Emergency Power Off (EPO) connector	✓
Input frequency *	40 - 70 Hz	SmartSlot	✓
Output operation voltage (min)	220 V	Battery	
Output operation voltage (max)	240 V	Battery technology	Sealed Lead Acid (VRLA)
Output frequency	50/60 Hz	Design	
Efficiency	92%	Form factor *	Rackmount
Emergency Power Off (EPO)	✓	Rack capacity	2U
Surge protection	✓	Product colour *	Black
Ports & interfaces		Display type	LCD
AC outlet types	C13 coupler, C19 coupler	Weight & dimensions	
Power plug	C20 coupler	Width	432 mm
AC outlets quantity	10 AC outlet(s)	Depth	635 mm
		Height	85 mm
		Weight	31.3 kg
		Logistics data	
		Harmonized System (HS) code	85078000



5415247273332



0731304330165



731304330165

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.