



Lenovo 55945KX uninterruptible power supply (UPS) Double-conversion (Online) 5 kVA 4500 W 10 AC outlet(s)



Brand : Lenovo

Product code: 55945KX

Product name : 55945KX

RT5kVA 3U Rack or Tower UPS (200-240VAC)

Lenovo 55945KX uninterruptible power supply (UPS) Double-conversion (Online) 5 kVA 4500 W 10 AC outlet(s):

The RT5kVA and RT6kVA 3U Rack or Tower Uninterruptible Power Supply (UPS) offerings provide extended power protection with increased efficiency and simplified power management to safeguard high-availability of Lenovo server environments. With efficiency ratings of up to 98%, these compact 3U rack or tower designs can help reduce energy usage without compromising performance or reliability. The 3U Rack or Tower UPS units can be installed in a data center rack cabinet or can be used as tower UPS units in office and distributed IT environments where extended power protection is required.

Features		Design	
UPS topology *	Double-conversion (Online)	Form factor *	Tower
Output power capacity *	5 kVA	Rack capacity	3U
Output power *	4500 W	Product colour *	Black
Input operation voltage (min) *	200 V	Control type	Buttons
Input operation voltage (max) *	240 V	LED indicators	✓
Input frequency *	50/60 Hz	Operational conditions	
Maximum current	25 A	Operating temperature (T-T)	0 - 40 °C
Ports & interfaces		Operating relative humidity (H-H)	0 - 95%
AC outlet types	C13 coupler, C19 coupler	Operating altitude	0 - 3000 m
AC outlets quantity	10 AC outlet(s)	Certificates	
USB port	✓	Certification	FCC UL CSA or cUL CE Mark NOM GOST BSMI Taiwan CB Report VCCI C-Tick (Australia) IRAM (Argentina)
USB port type	USB Type-B	Weight & dimensions	
RS-232 ports	1	Width	441 mm
Ethernet LAN (RJ-45) ports	1	Depth	685 mm
Battery		Height	130 mm
Battery technology	Sealed Lead Acid (VRLA)	Weight	48 kg
Hot-swap battery	✓		



0883436548137



883436548137

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.