



APC SRTG192XLBP4 UPS battery Sealed Lead Acid (VRLA) 192 V

Brand : APC
Product code: SRTG192XLBP4
Product name : SRTG192XLBP4

Smart-UPS RT Battery Pack 192V, rackmount, 3U

APC SRTG192XLBP4 UPS battery Sealed Lead Acid (VRLA) 192 V:

Extended Runtime
The SRTG192XLBP4 is an external runtime battery module from APC (Schneider Electric), designed as an ideal complement to SRTG models with 5kVA to 10kVA capacity. The module provides reliable, long-term power support for critical IT environments.

Form Factor
Comes standard as a tower model with stabilizing feet. With the optional rackmount brackets (SRTGRK1), the UPS can also be adapted for horizontal 19-inch rack mounting, occupying 3U/RU. Key Features:

Voltage: 192V DC, compatible with SRT 5kVA/6kVA/8kVA/10kVA SRTG On-Line UPS systems
Battery type: VRLA, with an expected lifespan of 3-5 years
Modular design: Includes 4 replaceable APCRBC174 battery cartridges
Expandable: Connect up to 4 battery packs for extended runtime



Features		Packaging data	
Battery technology *	Sealed Lead Acid (VRLA)	Package height	335 mm
Battery voltage *	192 V	Package depth	780 mm
Product colour	Black	Package weight	101.5 kg
Weight & dimensions		Operational conditions	
Weight	91 kg	Operating temperature (T-T)	0 - 40 °C
Width	440 mm	Operating relative humidity (H-H)	0 - 95%
Height	130 mm	Storage relative humidity (H-H)	0 - 95%
Depth	683 mm	Operating altitude	0 - 2011.68 m
Packaging data		Non-operating altitude	0 - 15240 m
Package width	580 mm		



0731304426264



731304426264

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.