



TP-Link Archer VR1210v wireless router Gigabit Ethernet Dual-band (2.4 GHz / 5 GHz) Black

Brand : TP-Link

Product code: ARCHER VR1210V V2.0

Product name : Archer VR1210v

- Super VDSL: The Latest Super VDSL (VDSL2 Profile 35b) tech delivers internet speeds of up to 350 Mbps
 - Speedy WiFi: Experience superb wireless connections with 867 Mbps (5 GHz) + 300 Mbps (2.4 GHz) dual band WiFi
 - Versatile Connectivity: Fully compatible with VDSL2/ADSL2+/ADSL2/ADSL standards, as well as fiber, cable, and 3G/4G internet services
 - Full Gigabit Ports: Take full advantage of broadband speeds up to 1 Gbps
 - Superior Range: Two fixed omnidirectional antennas with Beamforming technology provide stable wireless connections and optimal coverage
 - MU-MIMO Technology: Simultaneously transfers data to multiple devices to reduce congestion and boost the average throughput
 - Telephony: Make or receive phone calls over the internet simply by connecting the device to their existing telephone set
- Dual Band, Gigabit, VoIP, VDSL/ADSL, USB 3, black



WAN connection		Security	
Ethernet WAN *	✓	Stateful Packet Inspection (SPI)	✓
DSL WAN *	✓	Filtering	✓
SIM card slot *	✗	DMZ support	✓
3G/4G USB modem compatibility *	✓	Network address translation (NAT)	✓
WAN connection type	RJ-45	Protocols	
Wireless LAN features		DHCP client	✓
Wi-Fi band *	Dual-band (2.4 GHz / 5 GHz)	DHCP server	✓
Top Wi-Fi standard *	Wi-Fi 5 (802.11ac)	Universal Plug and Play (UPnP)	✓
WLAN data transfer rate (max) *	867 Mbit/s	Switching protocols	IPv4, IPv6
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)	Routing protocols	RIP-1, RIP-2
Channels quantity	2 channels	Management protocols	HTTP / HTTPS, SSL
Network		Design	
Ethernet LAN *	✓	Product colour	Black
Ethernet LAN interface type *	Gigabit Ethernet	Wall mountable	✓
Ethernet LAN data rates	10,100,1000 Mbit/s	LED indicators	LAN, Link, Power, Status, WAN
Cabling technology	10/100/1000Base-T(X)	On/off switch	✓
Networking standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, IEEE 802.3, IEEE 802.3ab, IEEE 802.3u	Product type *	Portable router
Port forwarding	✓	Certificates	
Port triggering	✓	Compliance certificates	CE, EAC, RoHS
Dynamic DNS (DDNS)	✓	Packaging content	
Static route	✓	AC adapter included	✓
USB sharing	✓	Manual	✓
Support Samba (storage)	✓	Sustainability	
		Sustainability compliance	✓

Network		Antenna	
Built-in FTP server	✓	Antenna design *	Internal
Media server	✓	Antenna gain level (max)	2 dBi
VPN support	OpenVPN, PPTP VPN, IPSec VPN	Antenna direction type	Omni-directional
DSL features		Features	
ADSL	✓	Firmware upgradeable	✓
ADSL2	✓	Power	
ADSL2+	✓	Power source type *	AC, DC
VDSL	✓	Output voltage	12 V
VDSL2	✓	Output current	1.5 A
Internal modem	✓	Operational conditions	
Ports & interfaces		Operating temperature (T-T)	0 - 40 °C
Ethernet LAN (RJ-45) ports *	4	Storage temperature (T-T)	-40 - 70 °C
USB port *	✓	Operating relative humidity (H-H)	10 - 90%
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity	1	Storage relative humidity (H-H)	5 - 90%
DC-in jack	✓	System requirements	
Management features		Windows operating systems supported	Windows 10, Windows 2000, Windows 7, Windows 8, Windows 8.1, Windows 98SE, Windows NT, Windows Vista, Windows XP
Web-based management	✓	Linux operating systems supported	✓
Wi-Fi Multimedia (WMM)/(WME)	✓	Mac operating systems supported	✓
Quality of Service (QoS) support	✓	Weight & dimensions	
Reset button	✓	Width	214 mm
WPS push button	✓	Depth	144.5 mm
MU-MIMO technology	✓	Height	80 mm
Security		Packaging data	
Security algorithms	64-bit WEP, 128-bit WEP, IPSec, WPA, WPA-PSK, WPA2, WPA-PSK2	Package type	Box
Firewall	✓		
Firewall security	NAT, SPI		
Guest access	✓		
Access Control List (ACL)	✓		



4897098685662

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.