



TP-Link Omada AX3000 Indoor/Outdoor WiFi 6 Access Point

Brand : TP-Link

Product family: Omada

Product code: EAP650-OUTDOOR

Product name : AX3000
Indoor/Outdoor WiFi 6 Access Point

2.4GHz (574Mbps), 5GHz (2402Mbps), 1x Gigabit Ethernet (RJ-45), Wi-Fi 6 802.11ax/ac/n/g/b/a, 280.4 x 106.5 x 56.8 mm

TP-Link Omada AX3000 Indoor/Outdoor WiFi 6 Access Point. 2.4 GHz, 5 GHz, Maximum data transfer rate: 3000 Mbit/s. Security algorithms: WPA, WPA-Enterprise, WPA2, WPA2-Enterprise, WPA3, WPA3-Enterprise. Ethernet LAN data rates: 10,100,1000 Mbit/s. Power over Ethernet (PoE). Product colour: White



Features		Ports & interfaces	
2.4 GHz *	✓	Ethernet LAN (RJ-45) ports *	1
5 GHz *	✓	Power	
6 GHz *	✗	Power over Ethernet (PoE) *	✓
Maximum data transfer rate *	3000 Mbit/s	Design	
Maximum data transfer rate (2.4 GHz)	574 Mbit/s	Placement *	Pole, Wall
Maximum data transfer rate (5 GHz)	2402 Mbit/s	Product colour *	White
Ethernet LAN data rates	10,100,1000 Mbit/s	International Protection (IP) code	IP67
Networking standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11ax, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, IEEE 802.1x, IEEE 802.3at	Reset button	✓
Cabling technology	10/100/1000Base-T(X)	LED indicators	✓
Number of users	250 user(s)	Antenna	
Automatic channel selection	✓	Antenna type *	Internal
Automatic channel scanning	✓	Antenna direction type	Omni-directional
MIMO	✓	Certificates	
MIMO type	Multi User MIMO	Certification	CE, FCC, RoHS
Fit AP mode features	Mesh networking	Weight & dimensions	
VLAN support	✓	Width	280.4 mm
Rate limiting	✓	Depth	106.5 mm
Band steering	✓	Height	56.8 mm
Airtime Fairness (ATF)	✓	Packaging content	
Quality of Service (QoS) support	✓	Quantity per pack	1 pc(s)
BeamForming	✓	Mounting kit	✓
Security		Quick start guide	✓
Security algorithms *		Operational conditions	
WPA, WPA-Enterprise, WPA2, WPA2-Enterprise, WPA3, WPA3-Enterprise		Operating relative humidity (H-H)	10 - 90%
		Operating temperature (T-T)	-30 - 70 °C


Security		Operational conditions	
MAC address filtering	✓	Storage temperature (T-T)	-40 - 70 °C
Service Set Identifier (SSID) features	Multiple SSIDs, SSID broadcast on/off	Storage relative humidity (H-H)	5 - 90%



4897098682098



4897098683552



0840030703553



840030703553

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.