ASUS ROG Swift XG32AQ computer monitor 81.3 cm (32") 2560 x 1440 pixels Wide Quad HD Black



Brand : ASUS

Product family: ROG Swift

Product code: 90LM08A0-B01170

Product name : XG32AQ

- 32 inch WQHD (2560 x 1440) monitor with ultrafast 175Hz (OC) refresh rate designed for professional gamers and immersive gameplay
- Fast IPS technology enables a 1ms response time (GTG) for sharp gaming visuals with high frame rates
- G-SYNC Compatible, delivering a seamless, tear-free gaming experience by enabling VRR (variable refresh rate) by default
- High dynamic range (HDR) technology with DisplayHDR™ 600 compliance combined with DCI-P3 color gamut ensures exceptional contrast and color performance
- Features an ergonomically designed stand to offer extensive swivel, tilt, and height adjustment

32" 2560 x 1440 IPS, 1ms, 1000:1, 175Hz, DisplayPort, HDMI, USB, 32W, 100 - 240V, 50/60 Hz



Display	
Display diagonal *	81.3 cm (32")
Display resolution *	2560 x 1440 pixels
HD type *	Wide Quad HD
Native aspect ratio *	16:9
Panel type *	IPS
Backlight type	LED
Touchscreen *	✗
Display brightness (peak)	600 cd/m²
Display brightness (typical)	450 cd/m²
Response time *	1 ms
Display surface	Matt
Screen shape *	Flat
Contrast ratio (typical) *	1000:1
Contrast ratio (dynamic)	100000000:1
Maximum refresh rate *	175 Hz
Viewing angle, horizontal	178°
Viewing angle, vertical	178°
Display number of colours *	1.073 billion colours
Pixel pitch	0.277 x 0.277 mm
Viewable size, horizontal	70.8 cm
Viewable size, vertical	39.9 cm
Digital horizontal frequency	250 - 250 kHz
Digital vertical frequency	48 - 175 Hz
High Dynamic Range (HDR) supported	✓
High Dynamic Range (HDR) technology	DisplayHDR 600
Colour gamut standard	DCI-P3
Colour gamut	96%

Ports & interfaces	
Built-in USB hub *	✓
USB Type-A downstream ports quantity	2
HDMI *	✓
HDMI ports quantity	2
HDMI version	2.0
DisplayPorts quantity	1
DisplayPort version	1.2
Headphone out *	✓
Headphone outputs	1
Headphone connectivity	3.5 mm
HDCP	✓
HDCP version	2.2

Ergonomics	
VESA mounting *	✓
Panel mounting interface	100 x 100 mm
Cable lock slot *	✓
Cable lock slot type	Kensington
Height adjustment *	✓
Adjustable height (max)	8 cm
Swivelling	✓
Swivel angle range	25 - -25°
Tilt angle range	20 - -5°

Power	
Energy efficiency class (SDR) *	F
Power consumption (typical) *	32 W
Power consumption (PowerSave)	0.5 W

Display	
sRGB coverage (typical)	130%

Performance	
NVIDIA G-SYNC *	✔
NVIDIA G-SYNC type	G-SYNC Compatible
AMD FreeSync *	✔
AMD FreeSync type	FreeSync Premium Pro
Flicker-free technology	✔
Low Blue Light technology	✔

Multimedia	
Built-in speaker(s) *	✘
Built-in camera *	✘

Design	
Market positioning *	Gaming
Product colour *	Black
Feet colour	Black

Power	
AC input voltage	100 - 240 V
AC input frequency	50 - 60 Hz

Weight & dimensions	
Width (with stand)	728.2 mm
Depth (with stand)	279.9 mm
Height (with stand)	539.9 mm
Weight (with stand)	8.9 kg
Width (without stand)	728.2 mm
Depth (without stand)	87.1 mm
Height (without stand)	428.5 mm
Weight (without stand)	5.77 kg

Packaging data	
Package width	900 mm
Package depth	226 mm
Package height	526 mm
Package weight	13 kg
Package type	Box



0195553847261



195553847261



4711081847236

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date