



APC SRV10KIL uninterruptible power supply (UPS) Double-conversion (Online) 10 kVA 10000 W

Brand : APC

Product code: SRV10KIL

Product name : SRV10KIL

LCD Multi-function, 10.0kWatts / 10.0kVA, 230V, Hard Wire 3-wire, 600J, 76.5kg
APC SRV10KIL. UPS topology: Double-conversion (Online), Output power capacity: 10 kVA, Output power: 10000 W. AC outlet types: Hard Wire 3-wire (1P + N + E), Serial interface type: RS-232. Form factor: Tower, Product colour: Black, Cooling type: Active. Compliance certificates: RoHS, Certification: CE, IEC 62040-1-1, IEC 62040-1-2. Cables included: USB cable




Features		Design	
UPS topology *	Double-conversion (Online)	Form factor *	Tower
Output power capacity *	10 kVA	Cooling type	Active
Output power *	10000 W	Built-in fan	✓
Waveform *	Sine	Product colour *	Black
Input operation voltage (min) *	220 V	Display type	LCD
Input operation voltage (max) *	240 V	LED indicators	Power, Status
Input frequency *	40/70 Hz	Operational conditions	
Output operation voltage (min)	220 V	Operating temperature (T-T)	0 - 40 °C
Output operation voltage (max)	240 V	Operating relative humidity (H-H)	0 - 95%
Surge energy rating	600 J	Storage relative humidity (H-H)	0 - 95%
Crest factor	3:1	Operating altitude	0 - 3000 m
Emergency Power Off (EPO)	✓	Non-operating altitude	0 - 14763 m
Surge protection	✓	Certificates	
Power protection features	Overload	Compliance certificates	RoHS
Audible alarm(s)	✓	Certification	CE, IEC 62040-1-1, IEC 62040-1-2
Ports & interfaces		Packaging content	
AC outlet types	Hard Wire 3-wire (1P + N + E)	Cables included	USB cable
USB port	✓	Management card included	✗
Serial interface	✓	Manual	✓
Serial interface type	RS-232	Weight & dimensions	
RS-232 ports	1	Width	380 mm
Emergency Power Off (EPO) connector	✓	Depth	485 mm
SmartSlot	✓		

Ports & interfaces		Weight & dimensions	
SmartConnect port	✖	Height	368 mm
		Weight	76.5 kg
		Packaging data	
		Package weight	82.5 kg
		Logistics data	
		Harmonized System (HS) code	85078000



0731304337942



731304337942



8592978368470

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.