

Targus THZ919GL tablet case 26.7 cm (10.5") Cover Black

Brand : Targus

Product code: THZ919GL

Product name : THZ919GL

For Galaxy Tab A8 10.5", TPU

Targus THZ919GL tablet case 26.7 cm (10.5") Cover Black:

Style and function come together to deliver protection and performance for your Samsung Galaxy® Tab A8 10.5". With military-grade protection for drops up to 1.2 metres (4 ft), this Click-In™ Case offers peace of mind in a sleek and stylish design. The patented custom-moulded tray secures and safeguards, while the elastic closure ensures safe travel.

A simple flip transforms your case into a sturdy stand for comfortable typing. Flip again for easy viewing with virtually infinite viewing angles. Enjoy added ease and convenience with the elastic stylus holder and Samsung S Pen® charging port, keeping your S Pen® ready to go or your stylus close at hand. Precision cutouts offer easy access to your controls, ports, and camera lenses. Even your audio gets a boost with dedicated speaker ports.

Targus THZ919GL. Case type: Cover, Brand compatibility: Samsung, Compatibility: Galaxy Tab A8, Maximum screen size: 26.7 cm (10.5"). Weight: 250 g



Features		Battery	
Compatibility *	Galaxy Tab A8	Built-in battery *	✗
Maximum screen size *	26.7 cm (10.5")	Weight & dimensions	
Case type *	Cover	Width	90 mm
Material *	Thermoplastic polyurethane (TPU)	Depth	160 mm
Product main colour *	Black	Height	250 mm
Brand compatibility *	Samsung	Weight	250 g
Built-in speaker(s) *	✗	Packaging data	
Stand mode *	✓	Quantity per pack	1 pc(s)
Country of origin	China	Logistics data	
		Harmonized System (HS) code	84733080



0092636361082



092636361082



5051794034622

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.