

StarTech.com 8 Port 1U Rackmount USB PS/2 KVM Switch with OSD

Brand : StarTech.com

Product code: SV831DUSBGB

Product name : 8 Port 1U Rackmount USB PS/2 KVM Switch with OSD

8 Port 1U Rackmount USB PS/2 KVM Switch with OSD
StarTech.com 8 Port 1U Rackmount USB PS/2 KVM Switch with OSD. Keyboard port type: USB, PS/2, Video port type: VGA. Maximum analog resolution: 1920 x 1440 pixels, Number of users: 1 user(s). Product colour: Black. Input voltage: 110-240 V. Width: 180 mm, Depth: 438 mm, Height: 45 mm



Ports & interfaces		Weight & dimensions	
Number of computers controlled *	8	Width	180 mm
Keyboard port type *	USB, PS/2	Depth	438 mm
Video port type *	VGA	Height	45 mm
Audio connections	✗	Weight	2.9 kg
DC-in jack	✓	Packaging data	
Performance		Package width	88 mm
Maximum analog resolution	1920 x 1440 pixels	Package depth	595 mm
Number of users	1 user(s)	Package height	264 mm
Design		Package weight	3.45 kg
Product colour *	Black	Packaging content	
Display		Cables included	PS/2
Built-in display *	✗	Manual	✓
Power		AC adapter included	✓
Input voltage	110-240 V	Other features	
Operational conditions		Connectivity technology	Wired
Operating temperature (T-T)	5 - 40 °C	Power supply type	110 - 240 V AC
Storage temperature (T-T)	-20 - 60 °C	Dimensions (WxDxH)	180 x 438 x 45 mm
Storage relative humidity (H-H)	0 - 80%	Ports quantity	8
		Logistics data	
		Harmonized System (HS) code	85176200



0065030823975



065030823975



5051964011736

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.