

Epson Squirrel Singlepack Cyan 378XL Claria Photo HD Ink

Brand : Epson

Product family: Squirrel

Product code: C13T37924010

Product name : Singlepack
Cyan 378XL Claria Photo HD Ink

Singlepack Cyan 378XL Claria Photo HD Ink
Epson Squirrel Singlepack Cyan 378XL Claria Photo HD Ink. Cartridge capacity: High (XL) Yield, Colour ink page yield: 830 pages, Colour ink volume: 9.3 ml, Printing colours: Cyan, Quantity per pack: 1 pc(s)



Features		Packaging data	
Print technology	Inkjet printing	Package type	Blister
Compatibility *	- Expression Photo XP-8500 - Expression Photo HD XP-15000	Other features	
Quantity per pack *	1 pc(s)	Certification	CE
Colour ink cartridges quantity	1	Logistics data	
Colour ink volume	9.3 ml	Products per pallet	2720 pc(s)
Colour ink page yield *	830 pages	Pallet gross weight	0 g
Type *	Original	Master (outer) case width	102 mm
Cartridge capacity	High (XL) Yield	Master (outer) case length	260 mm
Printing colours *	Cyan	Master (outer) case height	146 mm
Brand compatibility *	Epson	Products per master (outer) case	8 pc(s)
OEM code	C13T37924010	Master (outer) case gross weight	0 g
Country of origin	Indonesia	Master (outer) case GTIN (EAN/UPC)	8715946648804
Operational conditions		Harmonized System (HS) code	84439990
Storage temperature (T-T)	-20 - 40 °C	Pallet weight (UK)	0 g
Packaging data		Products per pallet (UK)	2720 pc(s)
Package width	102 mm	Products per pallet layer	272 pc(s)
Package depth	33 mm	Products per pallet layer (UK)	272 pc(s)
Package height	145 mm	Minimum order quantity	8 pc(s)
Package weight	47 g		



8715946645865



4058154242445

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.