



APC KVM-DVIVMCAC KVM switch Black

Brand : APC  
Product code: KVM-DVIVMCAC  
Product name : KVM-DVIVMCAC


- APC KVM 2G, SERVER MODULE, DVI WITH VIRTUAL MEDIA AND CAC
  - Manage multiple servers with just one keyboard, monitor and mouse
  - Occupies 1U of rack space - Conserve valuable rack space in the data center
  - Hot Pluggable Operation - Add or remove servers without having to power off the switch
  - Out-of-band management - Troubleshoot servers and diagnose problems in lieu of a working operating system with POST and BIOS-level access to servers
  - Scalable Architecture - Cascade multiple KVM switches for a modular solution that supports multiple platforms, improving flexibility and simplifying future expansion. Please see the user's manual for specific cascading capabilities
  - Multi-platform Support - Windows, Sun, Unix and Linux compatible
- APC KVM 2G, SERVER MODULE, DVI WITH VIRTUAL MEDIA AND CAC



| Ports & interfaces                |                                                                                     | Operational conditions          |          |
|-----------------------------------|-------------------------------------------------------------------------------------|---------------------------------|----------|
| DVI-I ports quantity              | 1                                                                                   | Storage relative humidity (H-H) | 5 - 95%  |
| Network                           |                                                                                     | Weight & dimensions             |          |
| Ethernet LAN (RJ-45) ports        | 1                                                                                   | Width                           | 125 mm   |
| Design                            |                                                                                     | Depth                           | 125 mm   |
| Product colour *                  | Black                                                                               | Height                          | 14 mm    |
| Certification                     | C-tick, CE, FCC Part 15 Class A, ICES-003, TAA compliance, UL 60950-1, VCCI Class A | Weight                          | 130 g    |
| Sustainability                    |                                                                                     | Packaging data                  |          |
| Compliance certificates           | RoHS                                                                                | Package width                   | 125 mm   |
| Operational conditions            |                                                                                     | Package depth                   | 129 mm   |
| Operating temperature (T-T)       | 0 - 50 °C                                                                           | Package height                  | 42 mm    |
| Storage temperature (T-T)         | -10 - 60 °C                                                                         | Package weight                  | 170 g    |
| Operating relative humidity (H-H) | 5 - 95%                                                                             | Logistics data                  |          |
|                                   |                                                                                     | Harmonized System (HS) code     | 85176200 |



0731304335139



731304335139



7612205035478

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.