



Canon PGI-580BK Pigment Black Ink Cartridge

Brand : Canon
Product code: 2078C001
Product name : PGI-580BK Pigment Black Ink Cartridge



- Pigment black ink offers clear and crisp text
 - Rich, deep blacks printing
 - Affordable price
 - Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges²
 - Genuine Canon Ink provides consistent quality prints 100% of the time²
 - Genuine Canon Ink is 100% reliable so you can print with less stress²
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PGI-580BK Pigment Black Ink Cartridge

Canon PGI-580BK Pigment Black Ink Cartridge:

This 11.2ml pigment black ink is used for printing high quality documents on plain paper and ensures crisp, sharply defined fonts for perfect text. Print up to 200 document A4 pages with a standard black ink cartridge at ISO/IEC 24711¹ standard.
Canon PGI-580BK Pigment Black Ink Cartridge. Black ink type: Pigment-based ink, Black ink volume: 11.2 ml, Printing colours: Black, Black ink page yield: 200 pages

Features		Features	
Black ink type	Pigment-based ink	Printing colours *	Black
Compatibility *	PIXMA TS6150 PIXMA TR7550 PIXMA TS8151 PIXMA TS9150 PIXMA TS6151 PIXMA TS8150 PIXMA TS8152 PIXMA TS9155 PIXMA TR8550	Brand compatibility *	Canon
		OEM code	PGI-580PGBK
Black ink cartridges quantity	1	Country of origin	Japan
Black ink volume	11.2 ml	Packaging data	
Black ink page yield *	200 pages	Package width	146 mm
Type *	Original	Package depth	68 mm
Ink type	Pigment-based ink	Package height	34 mm
		Package weight	48 g
		Logistics data	
		Harmonized System (HS) code	84439990



4549292087062

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.