EPSON

Epson DS-410 Sheet-fed scanner 600 x 600 DPI A4 Black, White

Brand : Epson

Product code: B11B249401BY

Product name : DS-410

215.9 x 3048mm, 600x600DPI, CIS, 50 - 209 g/m², 297x152x154mm, 2.5kg
Epson DS-410. Maximum scan size: 215.9 x 3048 mm, Optical scanning resolution: 600 x 600 DPI, Input colour depth: 10 bit. Scanner type: Sheet-fed scanner, Product colour: Black, White. Sensor type: CIS, Daily duty cycle (max): 3000 pages, Scan file formats: BMP, JPG, PDF, PNG, TIFF. Standard input capacity: 50 sheets. Maximum ISO A-series paper size: A4, Scanning media types supported: Business Card, Post Card(JPN), ISO A-series sizes (A0...A9): A4, A5, A6

Scanning	
Maximum scan size *	215.9 x 3048 mm
Optical scanning resolution *	600 x 600 DPI
Colour scanning	✔
Duplex scanning *	✔
Input colour depth	10 bit
Output colour depth	8 bit
ADF scan speed (b/w, A4)	26 ppm
ADF scan speed (colour, A4)	26 ppm

Design	
Scanner type *	Sheet-fed scanner
Product colour *	Black, White
Built-in display *	✘

Performance	
Sensor type *	CIS
Scan file formats	BMP, JPG, PDF, PNG, TIFF
Daily duty cycle (max) *	3000 pages
Scan drivers	ISIS, TWAIN, WIA

Input capacity	
Standard input capacity	50 sheets

Paper handling	
Scanning media types supported	Business Card, Post Card(JPN)
Maximum ISO A-series paper size *	A4
ISO A-series sizes (A0...A9)	A4, A5, A6
ISO B-series sizes (B0...B9)	B5, B6
Letter	✔
Legal	✔
Auto Document Feeder (ADF) media weight	50 - 209 g/m²

Ports & interfaces	
USB port *	✔

Ports & interfaces	
USB version	2.0
Standard interfaces	USB 2.0

Power	
Power supply type *	AC
Power consumption (off)	0.2 W
AC input frequency	50 - 60 Hz
Input voltage	100 - 120 V
Power supply	15 W

Weight & dimensions	
Width	297 mm
Depth	152 mm
Height	154 mm
Weight	2.5 kg

Packaging content	
Cables included	AC, USB
Bundled software	Document Capture Pro 2.0, Epson Scan 2

Sustainability	
Sustainability certificates	ENERGY STAR

System requirements	
Windows operating systems supported	✔
Mac operating systems supported	✔
Server operating systems supported	Windows Server 2003 R2, Windows Server 2008 R2, Windows Server 2012 R2

Operational conditions	
Operating temperature (T-T)	5 - 35 °C
Operating relative humidity (H-H)	15 - 80%
Storage relative humidity (H-H)	15 - 85%

Logistics data	
Harmonized System (HS) code	84716070

8715946638713

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date