


PCB HOLES

NH2854  
(ART NO. 732761)



TEMPERATURE: -25+70°C  
 WITHSTAND VOLTAGE: AC500V(50Hz) 1min  
 RATED LOAD: AV30V DC45V  
 INSERTION AND EXTRACTION FORCE: 3-35N  
 CONTACT RESISTANCE: ≤0.03u  
 INSULATION RESISTANCE: ≥100mΩ  
 LIFE: 5000 TIMES

\* Green Product \*

未标注公差: 0~6: ±0.1  
 6~20: ±0.2  
 20以上: ±0.3

NO	PART NAME	QTY	MATERIAL(THICK)	REMARK
7	NUT	1	H62Y	CuSn-PLATE
6	WASHER	1	H62Y t0.5	CuSn-PLATE
5	HOUSING	1	ABS-757	BLACK
4	SPRING TERMINAL	1	QSn6.5-0.1Y t0.4	Ag-PLATE
2	OUTER CONTACT	1	H62Y	Ni-PLATE
1	EARTH TERMINAL	1	H62Y t0.3	Ag-PLATE

DSND	DATE	SCAL: 2/1	NAME
张立捷	201608-31		ENCLOSED JACK
CHKD	DATE		CAT.NO. NH2854
APVD	DATE		DWN.NO.

永佳美有限公司 REGENT PRETTY LIMITED		UNIT: mm	004
----------------------------------	--	----------	-----