



NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
8	FERRULE	BRASS	1	NICKEL
7	CENTER PIN	PHOSPHOR BRONZE	1	GOLD
6	BODY	BRASS	1	NICKEL
5	BODY	BRASS	1	NICKEL
4	INSULATOR	TEFLON	1	
3	INNER RETAINING RING	STAINLESS	1	NICKEL
2	GASKET	S.L. RUBBER	1	
1	SHELL	BRASS	1	NICKEL

Dimensions Are In Millimeters
 Unless Otherwise Specified
 Tolerances

0.5-6 = ± 0.2
 6-30 = ± 0.4
 30-120 = ± 0.6
 120-315 = ± 1.0
 315-1000 = ± 1.6
 1000-2000 = ± 2.4

0603001	733616	0409078	REVERSE POLARITY SMA PLUG CRIMP TYPE FOR RG58/U CABLE
---------	--------	---------	--