



NO	DESCRIPTION	QTY	ITEM NO.	MATERIAL	PLATING
1	BODY	1	S-P15	BRASS	GOLD 3-5 $\mu$ " MIN.
2	DIELECTRIC	1	T-040041	TEFLON	-
3	CENTER PIN	1	S-AP15	BRASS	GOLD 3-5 $\mu$ " MIN.
4	GASKET	1	G-06001	RUBBER	-
5	RETAINING RING	1	CW-06001	BRASS	GOLD 3-5 $\mu$ " MIN.
6	SHELL	1	S-08001	BRASS	GOLD 3-5 $\mu$ " MIN.

Dimensions Are In Millimeters  
Unless Otherwise Specified

Tolerances

0.5-6	=	± 0.2
6-30	=	± 0.4
30-120	=	± 0.6
120-315	=	± 1.0
315-1000	=	± 1.6
1000-2000	=	± 2.4

CAT. XX-RF