



NO	DESCRIPTION	QTY	MATERIAL	PLATING
1	BODY	1	BRASS	GOLD 3-5 $\mu$ " MIN.
2	DIELECTRIC 1	1	TEFLON	-
3	DIELECTRIC 2	1	TEFLON	-
3	CENTER PIN	1	PHOSPHOR BRONZE	GOLD 10 $\mu$ " MIN.

Dimensions Are In Millimeters

Unless Otherwise Specified

Tolerances	0.5-6 = $\pm 0.2$
	6-30 = $\pm 0.4$
	30-120 = $\pm 0.6$
	120-315 = $\pm 1.0$
	315-1000 = $\pm 1.6$
	1000-2000 = $\pm 2.4$

RoHS COMPLIANT

0605044

P/N SC229CU-XGGT50

734239/0414086

SMC JACK TO SMA JACK