



| | |
|---|------------|
| ITEM-NO. (ITEM-NO.) | 890-232 |
| Cross section1 (Cross section / mm²) | 0.25 - 1.5 |
| Cross section2 (Cross section / AWG) | 22 - 16 |
| Strip length (Strip length / mm) | 9 |
| Measured voltage (Measured voltage / V) | 250 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 16 |
| Height (Height / mm) | 11.7 |
| Width (Width / mm) | 10.4 |
| Depth (Depth / mm) | 34.1 |
| COLOR (COLOR) | weiß |
| WEIGHT (WEIGHT / g) | 2 |