

ASUS ROG Strix XG32UQ computer monitor 81.3 cm (32") 3840 x 2160 pixels 4K Ultra HD LCD Black

Brand : ASUS

Product family: ROG Strix

Product code: 90LM08B0-B01170

Product name : XG32UQ



- 32-inch 4K UHD (3840 x 2160) Fast IPS professional gaming monitor with 160 Hz refresh rate (overclocking)
 - HDMI® 2.1 supports native 4K 120 Hz gaming without chroma subsampling (4:4:4) on PlayStation® 5 and Xbox Series X
 - NVIDIA® G-SYNC® compatible and exclusive Variable Overdrive technology deliver seamless, tear-free gaming
 - High dynamic range (HDR) technology with DisplayHDR™ 600 compliance combined with 96% DCI-P3 color gamut ensures exceptional contrast and color performance
 - Features an ergonomically designed stand to offer extensive swivel, tilt, and height adjustment
- ROG Strix XG32UQ HDMI 2.1 Gaming Monitor — 32", 4K UHD (3840 x 2160), Fast IPS, 160 Hz (OC), 1 ms GTG, NVIDIA G-SYNC compatible, FreeSync Premium Pro, Variable Overdrive, DisplayHDR 600, 96% DCI-P3, DisplayPort 1.4

Display		Ports & interfaces	
Display diagonal *	81.3 cm (32")	DisplayPort version	1.4
Display resolution *	3840 x 2160 pixels	Headphone out *	✓
HD type *	4K Ultra HD	Headphone outputs	1
Native aspect ratio *	16:9	Headphone connectivity	3.5 mm
Display technology *	LCD	Ergonomics	
Panel type *	IPS	VESA mounting *	✓
Backlight type	LED	Panel mounting interface	100 x 100 mm
Touchscreen *	✗	Wall mountable	✓
Display brightness (peak)	600 cd/m²	Cable lock slot *	✓
Display brightness (typical)	450 cd/m²	Cable lock slot type	Kensington
Response time *	1 ms	Height adjustment *	✓
Anti-glare screen	✓	Adjustable height (max)	8 cm
Screen shape *	Flat	Swivelling	✓
Contrast ratio (typical) *	1000:1	Swivel angle range	-20 - 20°
Contrast ratio (dynamic)	1000000:1	Tilt adjustment	✓
Maximum refresh rate *	160 Hz	Tilt angle range	-5 - 20°
Viewing angle, horizontal	178°	Power	
Viewing angle, vertical	178°	Energy efficiency class (SDR) *	F
Display number of colours *	1.073 billion colours	Energy efficiency class (HDR) *	G
Pixel pitch	0.1845 x 0.1845 mm	Energy consumption (SDR) per 1000 hours *	33 kWh
Viewable size, horizontal	70.8 cm	Energy consumption (HDR) per 1000 hours *	117 kWh
Viewable size, vertical	39.9 cm	Power consumption (typical) *	51 W
Digital horizontal frequency	30 - 350 kHz	Power consumption (off)	0.3 W
Digital vertical frequency	47 - 160 Hz	Power consumption (PowerSave)	0.5 W
High Dynamic Range (HDR) supported	✓	AC input voltage	100 - 240 V
High Dynamic Range (HDR) technology	DisplayHDR 600	AC input frequency	50 - 60 Hz
Colour depth	10 bit	Energy efficiency scale	A to G
Colour gamut standard	DCI-P3		
Colour gamut	96%		
sRGB coverage (typical)	130%		

Performance		Weight & dimensions	
NVIDIA G-SYNC *	✓	Width (with stand)	728.2 mm
NVIDIA G-SYNC type	G-SYNC Compatible	Depth (with stand)	279.9 mm
AMD FreeSync *	✓	Height (with stand)	539.9 mm
AMD FreeSync type	FreeSync Premium Pro	Weight (with stand)	8.9 kg
Flicker-free technology	✓	Width (without stand)	728.2 mm
Low Blue Light technology	✓	Depth (without stand)	87.1 mm
Game mode	✓	Height (without stand)	428.5 mm
		Weight (without stand)	5.77 kg
Multimedia		Packaging data	
Built-in speaker(s) *	✗	Package width	900 mm
Built-in camera *	✗	Package depth	226 mm
		Package height	526 mm
Design		Package weight	13.2 kg
Market positioning *	Gaming	Package type	Box
Product colour *	Black	Packaging content	
Front bezel colour	Black	Stand included	✓
Detachable stand	✓	Cables included	DisplayPort, HDMI, USB Type-A
Feet colour	Black	Screws included	✓
Ports & interfaces		Quick start guide	✓
Built-in USB hub *	✓	Other features	
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Shadow control	✓
USB Type-A downstream ports quantity	2	Motion blur reduction	✓
HDMI *	✓	Certification	TÜV Flicker-free TÜV Low Blue Light VESA DisplayHDR 600 AMD FreeSync Premium Pro G-SYNC Compatible
HDMI ports quantity	2		
HDMI version	2.1		
DisplayPorts quantity	1		



4711081848028



0195553848053



195553848053

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.