



SPECIFICATIONS

Current Rating: 3 Amperes

Insulation Resistance: 1000MΩ Min

Dielectric Withstanding: 600V AC/DC

Contact Resistance: 20mΩ Max.

Operating Temperature: -40°C to +105°C

MATERIALS

Contact Material: Copper Alloy

Contact Plating: Gold / Tin over Nickel

Insulator: Glass Filled Polyester (UL 94V-0)

P.B.T or Nylon-6T

All materials must be RoHS compliant.

Terminal Code	Dimensions(mm)		
	A	B	C
QA	10.20	5.20	2.50
XQB	10.80	5.80	2.50
QC	11.60	5.80	3.30
QD	12.60	6.80	3.30
QE	14.00	8.20	3.30
QF	14.80	9.00	3.30
QG	17.90	12.10	3.30
XQH	19.80	14.00	3.30
QJ	21.60	15.80	3.30
QK	22.80	17.00	3.30
QL	24.90	19.10	3.30
NP	11.60	6.00	3.10
NQ	11.80	6.00	3.30
NR	12.60	7.00	3.10
NS	13.50	8.00	3.00
NT	14.20	8.70	3.00
NU	16.00	10.50	3.00
NV	18.00	12.50	3.00
NW	20.00	14.50	3.00
TM	14.50	8.90	3.10
TN	11.30	5.50	3.30
TZ	11.80	5.70	3.60

Datenblatt passend zu folgenden Artikelnummern

10120514 / 10120516 / 10120518 / 10120520

10120168 / 10120169 / 10120170 / 10120171 / 10120172 / 10120173