



**Recommended P.C.Board Layout**

## SPECIFICATIONS

**Current Rating:** 3.0 Amp

**Dielectric Withstanding:** 1000V AC

**Insulation Resistance:** 5000MΩ Min

**Contact Resistance:** 4mΩ Max.

**Operating Temperature:**

Gold Plated: -55°C to +125°C

Tin Plated: -40°C to +105°C

**Soldering Temperature:** 260°C for 10 seconds

## MATERIALS

**Insulation Material:** PPS, UL 94V-0

**Contact Material:** Brass

**All materials must be RoHS compliant.**

Datenblatt passend zu folgenden Artikelnummern

10120536 / 10120538 / 10120540