




SPECIFICATIONS

Current Rating: 0.5 Amp
Dielectric Withstand: 250V AC
Insulator Resistance: 1000 MΩ min.
Contact Resistance: 30mΩ Max.
Operating Temperature: -40°C to + 105°C

MATERIALS

Insulator: Glass, UL94V-0
P.B.T
Contacts: Phosphor Bronze
All materials must be RoHS compliant.

No. of Contacts	Dimensions(mm)	
	A	B
06	8.01	2.54
08	9.28	3.81
10	10.55	5.08
12	11.82	6.35
14	13.09	7.62
16	14.36	8.89
20	16.90	11.43
22	18.17	12.70
26	20.71	15.24
30	23.25	17.78
34	25.79	20.32
40	29.60	24.13
44	32.14	26.67
50	35.95	30.48
60	42.30	36.83
68	47.38	41.91
80	55.00	49.53

ORDERING INFORMATION:

P/N 1 2 D08 - xxx G B
 1 2 3

1. TERMINATED HEIGHT:
"D08" H= 5.00mm AFTER ASSEMBLY
2. NO. OF CONTACTS:
006, 008, 010, 012, 014, 016, 020, 022,
026, 030, 034, 040, 044, 050, 060, 068,
080
3. CONTACT FINISH:
"G" FULL GOLD PLATED

Datenblatt passend für den Artikel
10120607 / 10120608 / 10120610 / 10120612 / 10120614 / 10120616 / 10120618