


Bauform R (=inverser Typ C), Stecker, gerade Type R (=inversed type C), male, straight

APFEL



Technische Daten:

Seite 172

Verfügbare Oberflächen:

Gütestufe 3 *

Gütestufe 2

Gütestufe 1

Technical specs:


page 172

Available finish:

Quality class 3 *

Quality class 2

Quality class 1



a = tail length
k = termination cross section

	T2.5	T	WAA	WAB
a=	2.5	4	13	13
k=	0.3 x 0.38	0.3 x 0.38	0.64 x 0.64	0.6 x 0.6
	WBA	WBB	W5	W7
a=	17	17	5	7.4
k=	0.64 x 0.64	0.6 x 0.6	0.6 x 0.60	0.6 x 0.60

Bestellcode : **A - R - M - x - x - x**
Ordercode :

Bitte „x“ durch unten geeignete Option ersetzen
Please replace „x“ with appropriate option listed below

1.

Bestückung

96abc*, 64ac*, 64ab, 32a, 48abc, 32ac*

Position with contacts

96abc*, 64ac*, 64ab, 32a, 48abc, 32ac*

2.

Ausführung a (Pinlänge)

T -4mm*
T2.5 -2.5mm
WAB -13mm*
WAA -13mm
WBB -17mm
WBA -17mm
W5 -5mm
W7 -7mm

Version a (tail length)

T -4mm*
T2.5 -2.5mm
WAB -13mm*
WAA -13mm
WBB -17mm
WBA -17mm
W5 -5mm
W7 -7mm

3.

Gütestufe

- -Stufe 3 *
2 -Stufe 2
1 -Stufe 1

Quality class

- -class 3 *
2 -class 2
1 -class 1

* Standard