



for x please insert :

T2.5; T; WAA; WAB; WBA; WBB; W5; W7

64poles = row a+b

32poles = row a+b, all even

Current rating: 20°C, 2A
70°C, 1A
100°C, 0.5A

Operating voltage: 250V rms

UL-File: E149341

	T2.5	T	WAA	WAB
a=	2.5	4	13	13
K=	0.3x0.38	0.3x1.38	0.64x0.64	0.6x0.6
	WBA	WBB	W5	W7
a=	17	17	5	7.4
K=	0.64x0.64	0.6x1.6	0.5x0.50	0.6x0.60

Änderung

Datum

Name

Datum

Name

Benennung

DIN41612 Connector
female, straight, Type B

Bearb.

11.07.02

Hellwig

Gepr.

11.07.02

Hellwig

Norm.

A-BF64ab-x
A-BF32ab-x

ASSMANN
Electronic Components

Zeichnungsnummer

ASS 1301 CO

Blatt

1/1

Ersatz für

Blatt

1

2

3

4

5

6

7