


NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BODY/CONTACT: BRASS PER JIS-C3604
2. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70 μ" MIN THICK OVER COPPER STRIKE
6. GOLD PL 1-3μ" OVER NICKEL PL 70 μ" MIN THICK OVER COPPER STRIKE

| | | | |
|----|-------------|----------|--------|
| 5 | Ferrule | Brass | Nickel |
| 4 | Shell | Brass | Nickel |
| 3 | Insulator | Teflon | White |
| 2 | Contact | Brass | Gold |
| 1 | Body | Brass | Nickel |
| NO | Description | Material | Finish |

Recommended Cable Stripping



- 1: Crimped Contact
Hex Crimp Size: .068"
- 2: Crimped Ferrule
Hex Crimp Size: .213"