


| | | | | | | | | | | | |
|---|----------------|------------|-------------------|-------|-----------|------|-------------------------------|--|---|---|----------------------------|
| A | 09 66 462 6811 | M3 | 2 | | | | | |  All Dim. in mm Orig. Size DIN A 4 | D-Sub male standard 37 poles with solder pins,nuts, board lock and grounding pins | Maßstab/ Scale 1,5:1 |
| | 09 66 462 7811 | M3 | 3 | | | | | | | | |
| | 09 66 462 5811 | M3 | 0,76 µm Au | | | | | | | | |
| | 09 66 462 6812 | 4-40 UNC | 2 | | | | | | | | |
| | 09 66 462 7812 | 4-40 UNC | 3 | | | | | | | | |
| | 09 66 462 5812 | 4-40 UNC | 0,76 µm Au | 29725 | 26-OCT-01 | JB | | | | | |
| | Part number | nut thread | Performance level | Mod. | Dat. | Name | HARTING EURL F-95972 Paris | | TB 09 66 462 X81X Sub. | Blatt/ Page 1 / | |