


Rating	3A 125VAC, 1.5A 250VAC cUL _{US} T85	Mounting Hole	Circuit Structure
Contact R	20m ohm Max.		
Insulation R	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1000V 1 minute		
Operation Tempature	-20°~85°		
Circuit	3P SPDT ON-ON		
		Thickness: 2.0 max.	







MATERIAL:


Frame: PBT

Base: PBT

Toggle: Nickel plated brass

Terminal: Silver plated copper



△	Date	Name	Descriptions			
Drawing	Check	Approval	SCI No.		Model Name	Mini Toggle Switch
蘇崇仁			Customer No.		Model No.	MTE102A1
5/10/06		3/1307	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	