



Rating	16A 125V AC 10A 250V AC
Contact resistance	50mΩ Max
Insulation resistance	DC 500V 100MΩ Min
Dielectric strength	AC 1500V 1 minute
Cut-out	

FEATURES

- * MATERIAL: Frame is nylon (UL flame: 94V-2). Terminals are silver plated brass.
- * Illuminated actuators are molded in PC, available with red, amber, green, blue and white colors.
- * Snap-in mounting, easy to install switch into panel.
- * Except lever type actuator (AP, BP, CP, DP, LP), waterproof cover is optional.
- * Standard dimension of housing height is 14.5mm, if look for shorter height, please refer to page 1-55, item R13-208 with housing height 12.0mm.
- * R13-112B9 & R13-112B9F: The LED is built with PCB for shifting to AC rating application.



Cut-out for X8 ROCKER	
------------------------------	--

ROCKER	
A, B, BF C, D, E, F, G, H, I	A5
A2 E2 F2	LP
A2B	A8, B8 B8F C8, D8 F8, E8
B2 B2F	B9 B9F
L L3	AP BP CP DP



Ordering number instruction

R13-112 [Color Code] - [Function Code]

FUNCTION	TERMINAL
Different button (按钮不同)	0 2 187° SQ 0 9 PC 1 2 SO
Illuminated / Different button (带灯/按钮不同)	
Momentary / Illuminated / Different button (弹回/带灯/按钮不同)	
Different position / Different button (动作特性不同/按钮不同)	
Waterproof (防水)	