

Push switches

Order code	Manufacturer code	Description
78-0030	n/a	MINIATURE RED PUSH SWITCH
78-0035	n/a	MINIATURE BLACK PUSH SWITCH
78-0040	n/a	MINIATURE GREEN PUSH SWITCH
78-0045	n/a	MINIATURE YELLOW PUSH SWITCH
78-0050	n/a	MINIATURE BLUE PUSH SWITCH
78-0055	n/a	MINIATURE WHITE PUSH SWITCH

Push switches	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

Miniature push switches

Photograph



Technical Specification*

Max. Voltage	:	60Vac
Max. Current Rating	:	250mA
Overall Length	:	28mm
Diameter	:	10.5mm
Panel Cutout	:	7mm

* - The details in this specification are suggestions and should not be exceeded.
DO NOT USE FOR INDUSTRIAL APPLICATIONS

Additional/Ordering Information

A range of Push to make switches (Push to close); Connections are made via solder terminations, it is suggested not to exceed 300°C and also not to heat the terminations for longer than 3 seconds.