

# Foot Switch

## SCI A18-4

### Specifications

|                       |   |                             |
|-----------------------|---|-----------------------------|
| Model No.             | : | A18-4                       |
| Contact Rating        | : | 5A 125V AC                  |
|                       | : | 3A 250V AC                  |
| Contact Resistance    | : | 50 m $\Omega$ max.          |
| Insulation Resistance | : | 100M $\Omega$ min. @500V DC |
| Dielectric Strength   | : | 1,000V AC 1 minute          |
| Circuit               | : | OFF-(ON)                    |
| Terminal Connection   | : | 2.5mm Jack Plug             |
| Dimensions            | : | 74mm x 75mm x 32mm          |

