

Security/Proximity Switch

Order code	Manufacturer code	Description
78-1672	CTE002	SURFACE MOUNTING PROXIMITY SWITCH (RC)

Security/Proximity Switch

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

Security & Warning devices



Surface mounting proximity switch

Specification

Contact form / style:	Normally Open
Switching Voltage:	48Vac Max.
Switching Current:	0.5A Max.
Switching Capacity:	10VA Max
Contact Resistance:	200m Ω Max.
Switching Distance:	18mm Max.
Operating Temperature:	-20°C ~ +65°C
Storage Temperature:	-40°C ~ +65°C
Case Material:	ABS epoxy resin
Lead Length:	300mm \pm 5.0

Dimensions (mm)

