

Common key operated switch

Order code: **79-0306**



Specifications – No. TS901-2

1. All zinc body and core – chrome plated
2. 2 tubular keys and 1 fixing nut
3. Both “keyed different” and “keyed alike” sets are available
4. Off/On (2 positions)
5. Contact rating: 2A 125VAC, 1A 250VAC
6. Contact resistance: 10 milli-ohms max.
7. Insulation resistance: 500 meg-ohms min.
8. Dielectric strength: 1000VAC 1 minute

