



Description:

A range of circular profile cables specifically designed for use in telephone systems.
Manufactured in the UK to BT specification CW1308.

Specification:

Maximum working voltage:	80V AC (up to 10Khz)
Conductor resistance @20°C:	97.8Ω/1000M
Capacitance (unbalanced):	500pF
Insulation resistance:	=>50MΩ at 20°C
Nominal diameter:	4-core 2.9mm
	6-core 4.4mm
	8-core 5.9mm

Order code	Cores	Conductor								Length
		A	B	C	D	E	F	G	H	
01-0770	4	White on Blue	Blue on White	White on Orange	Orange on White					100m
01-0775	6	White on Blue	Blue on White	White on Orange	Orange on White	White on Green	Green on White			100m
01-0780	8	White on Blue	Blue on White	White on Orange	Orange on White	White on Green	Green on White	White on Brown	Brown on White	100m
01-0795	8	White on Blue	Blue on White	White on Orange	Orange on White	White on Green	Green on White	White on Brown	Brown on White	500m