

December 2012

PRODUCT DATA SHEET

Product	Step & Tile Paint (Red and Black)
Type	A gloss alkyd based paint available in black and red.
Intended Use	For tiles, concrete and bricks. Not recommended for use on glazed or quarry tiles.
Special Features	Contains micronised red oxide or special black pigment for good opacity.
Preparation	The surface must be clean, smooth, sound, dry, free from wax, dust and contaminants. Any wax polish previously applied can be removed with white spirit, steel wool and a clean rag. Existing paint, not being removed should be sanded to provide a key and cleaned with white spirit or detergent.
Application	Use a good quality brush and apply evenly.
Coats	2 coat are usually sufficient. Sand lightly between coats if required.
Drying Time	4-8 hours depending on temperature and humidity.
Re-coating Time	Allow 6-8 hours between coats or overnight, depending on temperature and humidity.
Application Temp.	Ideally 15-25°C. Do not use below 10°C, or in conditions of high humidity.
Coverage	14 sq. metres per litre, per coat, depending on the absorbency of the surface.
Maintenance	Re-apply when surface becomes worn. The surface to be coated should be cleaned with a mild detergent solution or white spirit and lightly sanded to provide a key.
Compatibility	Can be applied over most solvent-based paints.
Settlement	STIR WELL BEFORE USE.
Shelf-life/Storage	Many years if stored in original, tightly closed container, in normal conditions.
Hazards	Flammable. Keep out of reach of children. Use only in well ventilated areas. Keep away from sources of ignition – no smoking. Avoid contact with skin and eyes. After contact with skin, wash immediately with plenty of soap and water or a proprietary skin cleanser. A full Safety Data Sheet is available upon request or on www.rustins.co.uk
Clean-Up	whilst wet with white spirit or Rustin's Brush Cleaner . Remove excess product from brushes before cleaning. Hard brushes can be cleaned with Rustin's Brush Restorer .
Sizes	250ml 500ml 1 L 2.5 L. Black not available in 2.5 L.