

Janitol® Original

Multi-Purpose Hard Surface Cleaner.

PRODUCT DESCRIPTION

A non-caustic, non-tainting, multi-purpose detergent for all general cleaning and degreasing applications.

INSTRUCTIONS FOR USE

For use on most washable hard surfaces. Apply by brush, mop, trigger sprayer, cloth, pressure washer or floor scrubber (See guide below).

DILUTION GUIDE

Can be used neat or diluted with water depending on surface to be cleaned

- Dilute 1:80 - 1:40 (1.2% - 2.5%) for general cleaning & degreasing
- Dilute 1:40 - 1:10 (2.5% - 10%) for heavy cleaning & degreasing
- Dilute 1:80 - 1:10 (1.2% - 10%) for floor scrubbing machinery
- The use of hot water will increase the product's cleaning ability.

SPILLAGE

In the case of spillage, mop up bulk and dilute remainder to foul drain with water. Treat large spillages as industrial waste.

STORAGE:

Store in original sealed container. Avoid extremes of temperature. This packaging is recyclable or can be disposed of, if well drained, as normal domestic or industrial waste.



FEATURES	BENEFITS
Versatile Cleaner	for use on all hard surfaces in all industrial environments including the food industry.
Non-caustic, Non-solvent	Less aggressive on sensitive surfaces; will not damage paintwork, varnish and other surfaces when used as instructed.
Non-Flammable	No restrictions on use or storage.
Concentrated Formula	Use according to cleaning performance required - see dilution guide above.
Non-perfumed	Suitable for use in environments where perfumes are not preferred, eg food handling areas.
Low Odour	No unpleasant odour during use, ideal for prolonged usage or use in enclosed spaces.
Liquid format formula	Mixes readily with water, without clogging jets or equipment.
Free Rinsing	Rinses completely away from surfaces leaving no residue.

PACK SIZES

STOCK CODE	SIZE
JAN600	5 litre
JAN76V	25 litre

SC Johnson Professional Ltd.
 Denby Hall Way
 Denby
 Derbyshire DE5 8JZ
 UK
 Tel: +44 (0) 1773 855100
 www.scjp.com

This information and all further technical advice is based upon our present knowledge and experience. However, it implies no liability or other legal responsibility on our part, including with regard to existing third party intellectual property rights, especially patent rights. In particular, no warranty, whether express or implied, or guarantee of product properties in the legal sense is intended or implied. We reserve the right to make any changes according to technological progress or further developments.